

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1290594

Luminaire Tested: P3A05R55W2N902765DE010 E3DLP1WMH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1290594
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R55W2N902765DE010 E3DLP1WMH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 3000K CCT AND, 90CRI ,
E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 288.0 lumens
Efficiency: N/A
Efficacy: 48.8 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1290594

CATALOG NUMBER: P3A05R55W2N902765DE010 E3DLP1WMH_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1290594

CATALOG NUMBER: P3A05R55W2N902765DE010 E3DLP1WMH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		97	95	94	92
2	107	102	97	94	105	100	96	93	97	93	91		94	91	89		91	89	87	85
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85	83	80	79
4	96	88	82	77	94	87	81	77	84	80	76		82	78	75		80	77	74	73
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76	72	69	67
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72	67	64	63
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68	63	60	59
8	78	68	62	57	76	67	61	57	66	61	57		65	60	57		64	60	56	55
9	74	64	58	54	73	63	58	54	62	57	53		62	57	53		61	56	53	52
10	70	60	54	51	69	60	54	50	59	54	50		58	54	50		58	53	50	49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	78349
5°	76381
10°	71007
15°	63224
20°	53741
25°	43357
30°	33068
35°	23503
40°	15515
45°	9210
50°	5390
55°	3326
60°	2938
65°	2646
70°	2308
75°	2033
80°	2020
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 9210 cd/sqm

TEST NUMBER: P1290594

CATALOG NUMBER: P3A05R55W2N902765DE010 E3DLP1WMH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	32.2	11.2
10°-20°	77.2	26.8
20°-30°	81.8	28.4
30°-40°	55.3	19.2
40°-50°	24.2	8.4
50°-60°	8.7	3.0
60°-70°	5.1	1.8
70°-80°	2.7	0.9
80°-90°	0.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	191.2	66.4
0°-40°	246.5	85.6
0°-60°	279.4	97.0
0°-90°	288.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	288.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	357	
5°	347	32
15°	278	77
25°	179	82
35°	88	55
45°	30	24
55°	9	9
65°	5	5
75°	2	3
85°	1	1
90°	0	

TEST NUMBER: P1290594

CATALOG NUMBER: P3A05R55W2N902765DE010 E3DLP1WMH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	357.3
2.5°	354.5
5°	347.0
7.5°	334.7
10°	318.9
12.5°	299.9
15°	278.5
17.5°	254.8
20°	230.3
22.5°	204.6
25°	179.2
27.5°	154.3
30°	130.6
32.5°	108.0
35°	87.8
37.5°	69.6
40°	54.2
42.5°	40.8
45°	29.7
47.5°	21.8
50°	15.8
52.5°	11.1
55°	8.7
57.5°	7.9
60°	6.7
62.5°	5.9
65°	5.1
67.5°	4.4
70°	3.6
72.5°	3.2
75°	2.4
77.5°	2.0
80°	1.6
82.5°	1.2
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)