

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1303726

Luminaire Tested: P3DUS13R509040DE010 E3CBUS1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1303726
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-91)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3DUS13R509040DE010 E3CBUS1MW
Description: 3in Adjustable LED luminaire with, R50 optic, 4000K CCT AND, 90CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1517.0 lumens
Efficiency: N/A
Efficacy: 103.9 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 0.71 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1303726

CATALOG NUMBER: P3DUS13R509040DE010 E3CBUS1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1303726

CATALOG NUMBER: P3DUS13R509040DE010 E3CBUS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	105	102	99	108	104	101	98	101	98	96		98	96	94		95	93	92	90
3	105	100	95	92	103	98	94	91	96	93	90		93	91	89		91	89	87	86
4	101	95	90	86	99	93	89	86	91	88	85		89	86	84		88	85	83	82
5	97	90	85	81	95	89	84	81	87	83	80		86	82	79		84	81	79	78
6	93	85	80	77	92	85	80	76	83	79	76		82	78	75		81	78	75	74
7	89	81	76	73	88	81	76	73	80	75	72		79	75	72		77	74	72	70
8	86	78	73	69	85	77	72	69	76	72	69		75	71	69		74	71	68	67
9	83	74	69	66	82	74	69	66	73	69	66		72	68	65		71	68	65	64
10	79	71	66	63	79	71	66	63	70	66	63		69	65	63		69	65	62	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	611618
5°	596961
10°	563940
15°	495621
20°	372829
25°	275653
30°	167216
35°	55278
40°	9733
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 0 cd/sqm

TEST NUMBER: P1303726

CATALOG NUMBER: P3DUS13R509040DE010 E3CBUS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	253.2	16.7
10°-20°	593.7	39.1
20°-30°	509.1	33.6
30°-40°	157.0	10.4
40°-50°	3.9	0.3
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1356.1	89.4
0°-40°	1513.1	99.7
0°-60°	1517.0	100.0
0°-90°	1517.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1517.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2789	
5°	2712	253
15°	2183	594
25°	1139	509
35°	206	157
45°	0	4
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1303726

CATALOG NUMBER: P3DUS13R509040DE010 E3CBUS1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	2789.2
2.5°	2768.7
5°	2712.0
7.5°	2632.6
10°	2532.7
12.5°	2373.8
15°	2183.2
17.5°	1940.4
20°	1597.7
22.5°	1307.2
25°	1139.3
27.5°	925.9
30°	660.4
32.5°	401.7
35°	206.5
37.5°	93.0
40°	34.0
42.5°	4.5
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)