

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1290615

Luminaire Tested: P3A05R60W2N902750DE010 E3CD1MB\_3000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1290615  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRIS  
Catalog Number: P3A05R60W2N902750DE010 E3CD1MB\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 3000K CCT AND, 90CRI ,  
E3CD1MB TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 511.0 lumens  
Efficiency: N/A  
Efficacy: 86.6 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1290615  
CATALOG NUMBER: P3A05R60W2N902750DE010 E3CD1MB\_3000K

### Luminous Intensity Polar Plot







TEST NUMBER: P1290615

CATALOG NUMBER: P3A05R60W2N902750DE010 E3CD1MB\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	51.2	10.0
10°-20°	147.4	28.8
20°-30°	171.9	33.6
30°-40°	110.9	21.7
40°-50°	24.9	4.9
50°-60°	2.5	0.5
60°-70°	1.2	0.2
70°-80°	0.7	0.1
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	370.6	72.5
0°-40°	481.5	94.2
0°-60°	508.9	99.6
0°-90°	511.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	511.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	556	
5°	532	51
15°	538	147
25°	376	172
35°	179	111
45°	27	25
55°	2	3
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1290615  
CATALOG NUMBER: P3A05R60W2N902750DE010 E3CD1MB\_3000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	556.5
2.5°	547.4
5°	532.4
7.5°	531.6
10°	541.9
12.5°	548.6
15°	538.3
17.5°	507.5
20°	462.4
22.5°	415.4
25°	375.9
27.5°	337.1
30°	291.3
32.5°	237.5
35°	179.4
37.5°	122.5
40°	77.1
42.5°	46.2
45°	27.3
47.5°	15.8
50°	8.3
52.5°	2.8
55°	2.0
57.5°	1.6
60°	1.6
62.5°	1.2
65°	1.2
67.5°	1.2
70°	0.8
72.5°	0.8
75°	0.8
77.5°	0.4
80°	0.4
82.5°	0.4
85°	0.4
87.5°	0.0
90°	0.0

(END OF REPORT)