

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1290630

Luminaire Tested: P3A05R60W2N902750DE010 E3D1H_3000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1290630
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R60W2N902750DE010 E3D1H_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 3000K CCT AND, 90CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 474.0 lumens
Efficiency: N/A
Efficacy: 80.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1290630
CATALOG NUMBER: P3A05R60W2N902750DE010 E3D1H_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1290630
 CATALOG NUMBER: P3A05R60W2N902750DE010 E3D1H_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.3	10.6
10°-20°	136.9	28.9
20°-30°	171.5	36.2
30°-40°	95.9	20.2
40°-50°	18.2	3.8
50°-60°	1.0	0.2
60°-70°	0.2	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	358.7	75.7
0°-40°	454.6	95.9
0°-60°	473.7	99.9
0°-90°	474.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	474.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	566	
5°	533	50
15°	492	137
25°	383	171
35°	153	96
45°	21	18
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1290630
CATALOG NUMBER: P3A05R60W2N902750DE010 E3D1H_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	566.4
1°	564.0
2°	556.7
3°	548.0
4°	539.8
5°	532.6
6°	527.2
7°	522.6
8°	519.1
9°	515.8
10°	512.9
11°	509.9
12°	506.7
13°	502.6
14°	497.7
15°	491.5
16°	484.0
17°	475.4
18°	465.7
19°	454.7
20°	444.6
21°	433.7
22°	422.5
23°	410.7
24°	397.7
25°	383.3
26°	366.5
27°	347.7
28°	326.5
29°	304.0
30°	279.8
31°	255.4
32°	230.2
32.5°	216.4
33°	204.0
34°	178.2
35°	152.8
36°	129.9
37°	105.7
37.5°	94.6
38°	83.8
39°	67.5
40°	55.5
42.5°	33.7
45°	21.3



TEST NUMBER: P1290630
CATALOG NUMBER: P3A05R60W2N902750DE010 E3D1H_3000K

CANDELA DISTRIBUTION (continued):

	0°
47.5°	11.8
50°	4.3
52.5°	1.0
55°	0.6
57.5°	0.4
60°	0.4
62.5°	0.2
65°	0.2
67.5°	0.2
70°	0.2
72.5°	0.2
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)