

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1290811

Luminaire Tested: P3A05R60W2N902765DE010 E3DL1GPH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1290811
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R60W2N902765DE010 E3DL1GPH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 3000K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 204.0 lumens
Efficiency: N/A
Efficacy: 34.6 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1290811

CATALOG NUMBER: P3A05R60W2N902765DE010 E3DL1GPH_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1290811

CATALOG NUMBER: P3A05R60W2N902765DE010 E3DL1GPH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20				20				20
RC	80				70				50				30				10				0				0				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100											
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93											
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85											
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	80	79											
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	75	73											
5	91	82	76	71	89	81	75	71	79	74	70	78	73	70	76	72	69	68											
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	67	64	63											
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	67	63	60	59											
8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55											
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51											
10	70	60	54	50	69	60	54	50	59	53	50	58	53	50	57	53	49	48											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	48176
5°	47722
10°	46314
15°	43405
20°	38410
25°	32131
30°	25194
35°	18257
40°	12166
45°	7567
50°	4094
55°	1185
60°	1096
65°	986
70°	1026
75°	1017
80°	1010
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 7567 cd/sqm

TEST NUMBER: P1290811

CATALOG NUMBER: P3A05R60W2N902765DE010 E3DL1GPH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	20.4	10.0
10°-20°	53.0	26.0
20°-30°	60.4	29.6
30°-40°	42.9	21.0
40°-50°	19.4	9.5
50°-60°	4.1	2.0
60°-70°	2.0	1.0
70°-80°	1.3	0.6
80°-90°	0.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	133.9	65.6
0°-40°	176.8	86.7
0°-60°	200.3	98.2
0°-90°	204.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	204.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	220	
5°	217	20
15°	191	53
25°	133	60
35°	68	43
45°	24	19
55°	3	4
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1290811

CATALOG NUMBER: P3A05R60W2N902765DE010 E3DL1GPH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	219.7
2.5°	218.9
5°	216.8
7.5°	213.1
10°	208.0
12.5°	200.9
15°	191.2
17.5°	179.0
20°	164.6
22.5°	149.1
25°	132.8
27.5°	116.1
30°	99.5
32.5°	83.6
35°	68.2
37.5°	54.7
40°	42.5
42.5°	32.2
45°	24.4
47.5°	18.2
50°	12.0
52.5°	5.6
55°	3.1
57.5°	2.7
60°	2.5
62.5°	2.3
65°	1.9
67.5°	1.7
70°	1.6
72.5°	1.4
75°	1.2
77.5°	1.0
80°	0.8
82.5°	0.6
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)