

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1304394

Luminaire Tested: P3DUS13R709735DE010 E3CBUS1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1304394
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-95)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3DUS13R709735DE010 E3CBUS1MW
Description: 3in Adjustable LED luminaire with, R70 optic, 3500K CCT AND, 97CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1137.0 lumens
Efficiency: N/A
Efficacy: 77.9 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.99
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1304394

CATALOG NUMBER: P3DUS13R709735DE010 E3CBUS1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1304394

CATALOG NUMBER: P3DUS13R709735DE010 E3CBUS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	108	106		111	109	107	105		105	103	101		101	100	98		98	96	95
2	108	103	99	96		106	102	98	95		98	95	93		95	93	91		93	91	89
3	103	96	91	88		101	95	90	87		92	89	85		90	87	84		88	85	83
4	98	90	85	80		96	89	84	80		87	82	79		85	81	78		83	80	77
5	93	84	79	74		91	83	78	74		82	77	73		80	76	73		78	75	72
6	88	79	73	69		86	78	73	69		77	72	68		75	71	68		74	70	67
7	83	74	68	64		82	74	68	64		72	67	64		71	67	63		70	66	63
8	79	70	64	60		78	69	64	60		68	63	59		67	62	59		66	62	59
9	75	66	60	56		74	65	60	56		64	59	56		63	59	55		63	58	55
10	72	62	56	52		71	62	56	52		61	56	52		60	55	52		59	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	276513
5°	263283
10°	251877
15°	240274
20°	222199
25°	201350
30°	173850
35°	156413
40°	60828
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 0 cd/sqm

TEST NUMBER: P1304394

CATALOG NUMBER: P3DUS13R709735DE010 E3CBUS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.2	9.9
10°-20°	295.7	26.0
20°-30°	378.3	33.3
30°-40°	326.6	28.7
40°-50°	24.3	2.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	786.2	69.1
0°-40°	1112.7	97.9
0°-60°	1137.0	100.0
0°-90°	1137.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1137.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1261	
5°	1196	112
15°	1058	296
25°	832	378
35°	584	327
45°	0	24
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1304394

CATALOG NUMBER: P3DUS13R709735DE010 E3CBUS1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1261.0
2.5°	1241.4
5°	1196.1
7.5°	1156.8
10°	1131.2
12.5°	1099.7
15°	1058.4
17.5°	1009.2
20°	952.2
22.5°	889.2
25°	832.2
27.5°	759.4
30°	686.6
32.5°	657.1
35°	584.3
37.5°	424.9
40°	212.5
42.5°	27.5
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)