

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1290889

Luminaire Tested: P3A05R60W2N902765DE010 E3DLP1H_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1290889
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R60W2N902765DE010 E3DLP1H_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 3000K CCT AND, 90CRI ,
E3DLP1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 288.0 lumens
Efficiency: N/A
Efficacy: 48.8 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1290889
CATALOG NUMBER: P3A05R60W2N902765DE010 E3DLP1H_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1290889
 CATALOG NUMBER: P3A05R60W2N902765DE010 E3DLP1H_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92			
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	79	78			
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72			
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66			
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62			
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57			
8	77	67	60	56	75	66	60	56	65	60	56	64	59	55	63	58	55	54			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50			
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	72999
5°	71340
10°	66799
15°	59932
20°	51524
25°	42607
30°	33676
35°	25002
40°	17232
45°	10792
50°	5936
55°	3479
60°	3114
65°	2646
70°	2308
75°	2372
80°	2020
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10792 cd/sqm



TEST NUMBER: P1290889

CATALOG NUMBER: P3A05R60W2N902765DE010 E3DLP1H_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	30.2	10.5
10°-20°	73.3	25.5
20°-30°	80.4	27.9
30°-40°	58.6	20.3
40°-50°	27.7	9.6
50°-60°	9.1	3.1
60°-70°	5.1	1.8
70°-80°	2.8	1.0
80°-90°	0.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	183.9	63.9
0°-40°	242.5	84.2
0°-60°	279.2	96.9
0°-90°	288.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	288.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	333	
5°	324	30
15°	264	73
25°	176	80
35°	93	59
45°	35	28
55°	9	9
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1290889

CATALOG NUMBER: P3A05R60W2N902765DE010 E3DLP1H_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	332.9
2.5°	330.9
5°	324.1
7.5°	313.9
10°	300.0
12.5°	283.4
15°	264.0
17.5°	243.0
20°	220.8
22.5°	198.3
25°	176.1
27.5°	154.0
30°	133.0
32.5°	112.8
35°	93.4
37.5°	76.0
40°	60.2
42.5°	46.3
45°	34.8
47.5°	25.3
50°	17.4
52.5°	11.5
55°	9.1
57.5°	7.9
60°	7.1
62.5°	5.9
65°	5.1
67.5°	4.4
70°	3.6
72.5°	3.2
75°	2.8
77.5°	2.0
80°	1.6
82.5°	1.2
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)