

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1304528

Luminaire Tested: P3DUS09R409740DE010 E3CBUS1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1304528
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-90)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3DUS09R409740DE010 E3CBUS1MW
Description: 3in Adjustable LED luminaire with, R40 optic, 4000K CCT AND, 97CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1041.0 lumens
Efficiency: N/A
Efficacy: 93.8 lumens/watt
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.55
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1304528
CATALOG NUMBER: P3DUS09R409740DE010 E3CBUS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1304528
 CATALOG NUMBER: P3DUS09R409740DE010 E3CBUS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	100
1	115	113	111	109	113	111	109	107	107	105	104	103	102	101	100	99	98	97	96	94	96
2	111	107	104	102	109	106	103	101	103	100	98	100	98	96	97	96	94	94	93	91	93
3	107	103	99	96	106	101	98	95	99	96	94	97	94	92	94	93	91	94	93	91	90
4	104	98	94	91	102	97	94	91	95	92	90	94	91	89	92	90	88	92	90	88	87
5	101	95	90	87	99	94	90	87	92	89	86	91	88	86	89	87	85	89	87	85	84
6	98	91	87	84	96	90	86	84	89	86	83	88	85	83	87	84	82	87	84	82	81
7	95	88	84	81	94	87	83	80	86	83	80	85	82	80	84	81	79	84	81	79	78
8	92	85	81	78	91	85	80	78	84	80	77	83	79	77	82	79	77	82	79	77	76
9	89	82	78	75	88	82	78	75	81	77	75	80	77	75	80	77	74	80	77	74	73
10	87	80	76	73	86	79	75	73	79	75	73	78	75	72	77	74	72	77	74	72	71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	640036
5°	634029
10°	596159
15°	491195
20°	272020
25°	78876
30°	19471
35°	6987
40°	1775
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 0 cd/sqm



TEST NUMBER: P1304528
 CATALOG NUMBER: P3DUS09R409740DE010 E3CBUS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	268.7	25.8
10°-20°	566.3	54.4
20°-30°	186.4	17.9
30°-40°	18.8	1.8
40°-50°	0.8	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1021.4	98.1
0°-40°	1040.2	99.9
0°-60°	1041.0	100.0
0°-90°	1041.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1041.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2919	
5°	2880	269
15°	2164	566
25°	326	186
35°	26	19
45°	0	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1304528
CATALOG NUMBER: P3DUS09R409740DE010 E3CBUS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2918.8
2.5°	2914.2
5°	2880.4
7.5°	2809.6
10°	2677.4
12.5°	2472.8
15°	2163.7
17.5°	1737.8
20°	1165.7
22.5°	629.0
25°	326.0
27.5°	155.3
30°	76.9
32.5°	43.1
35°	26.1
37.5°	13.8
40°	6.2
42.5°	1.5
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)