

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1290895

Luminaire Tested: P3A05R60W2N902765DE010 E3DLP1LI_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1290895
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R60W2N902765DE010 E3DLP1LI_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 3000K CCT AND, 90CRI ,
E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 288.0 lumens
Efficiency: N/A
Efficacy: 48.8 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1290895

CATALOG NUMBER: P3A05R60W2N902765DE010 E3DLP1LI_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1290895

CATALOG NUMBER: P3A05R60W2N902765DE010 E3DLP1LI_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	105		110	108	105	103		104	102	100		100	98	97		96	95	94
2	107	101	97	93		104	100	96	92		96	93	90		93	91	88		91	88	86
3	101	94	88	84		99	92	87	83		90	86	82		87	84	81		85	82	79
4	95	87	81	77		93	86	80	76		84	79	75		82	78	74		80	76	73
5	90	81	75	70		88	80	74	70		78	73	69		77	72	69		75	71	68
6	85	76	69	65		84	75	69	65		73	68	64		72	67	64		71	66	63
7	81	71	65	60		79	70	64	60		69	64	60		68	63	59		67	62	59
8	77	67	60	56		75	66	60	56		65	60	56		64	59	55		63	58	55
9	73	63	57	52		72	62	56	52		61	56	52		60	55	52		60	55	52
10	69	59	53	49		68	59	53	49		58	53	49		57	52	49		56	52	49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	72999
5°	71340
10°	66799
15°	59932
20°	51524
25°	42607
30°	33676
35°	25002
40°	17232
45°	10792
50°	5936
55°	3479
60°	3114
65°	2646
70°	2308
75°	2372
80°	2020
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 10792 cd/sqm

TEST NUMBER: P1290895

CATALOG NUMBER: P3A05R60W2N902765DE010 E3DLP1LI_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	30.2	10.5
10°-20°	73.3	25.5
20°-30°	80.4	27.9
30°-40°	58.6	20.3
40°-50°	27.7	9.6
50°-60°	9.1	3.1
60°-70°	5.1	1.8
70°-80°	2.8	1.0
80°-90°	0.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	183.9	63.9
0°-40°	242.5	84.2
0°-60°	279.2	96.9
0°-90°	288.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	288.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	333	
5°	324	30
15°	264	73
25°	176	80
35°	93	59
45°	35	28
55°	9	9
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1290895

CATALOG NUMBER: P3A05R60W2N902765DE010 E3DLP1LI_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	332.9
2.5°	330.9
5°	324.1
7.5°	313.9
10°	300.0
12.5°	283.4
15°	264.0
17.5°	243.0
20°	220.8
22.5°	198.3
25°	176.1
27.5°	154.0
30°	133.0
32.5°	112.8
35°	93.4
37.5°	76.0
40°	60.2
42.5°	46.3
45°	34.8
47.5°	25.3
50°	17.4
52.5°	11.5
55°	9.1
57.5°	7.9
60°	7.1
62.5°	5.9
65°	5.1
67.5°	4.4
70°	3.6
72.5°	3.2
75°	2.8
77.5°	2.0
80°	1.6
82.5°	1.2
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)