

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1290911

Luminaire Tested: P3A05R60W2N902765DE010 E3DLP1WH_6500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1290911
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R60W2N902765DE010 E3DLP1WH_6500K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 6500K CCT AND, 90CRI ,
E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 420.0 lumens
Efficiency: N/A
Efficacy: 71.2 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1290911

CATALOG NUMBER: P3A05R60W2N902765DE010 E3DLP1WH_6500K

Luminous Intensity Polar Plot



TEST NUMBER: P1290911

CATALOG NUMBER: P3A05R60W2N902765DE010 E3DLP1WH_6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93		
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85		
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	80	79		
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	75	73		
5	91	82	76	71	89	81	75	71	79	74	70	78	73	70	76	72	69	68		
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	68	64	63		
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	67	63	60	59		
8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55		
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51		
10	70	60	54	50	69	60	54	50	59	53	50	58	53	50	57	53	49	48		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	99181
5°	98239
10°	95367
15°	89354
20°	79084
25°	66149
30°	51856
35°	37611
40°	25018
45°	15599
50°	8426
55°	2447
60°	2281
65°	2075
70°	2052
75°	2033
80°	2020
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 15599 cd/sqm

TEST NUMBER: P1290911

CATALOG NUMBER: P3A05R60W2N902765DE010 E3DLP1WH_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.0	10.0
10°-20°	109.2	26.0
20°-30°	124.5	29.6
30°-40°	88.3	21.0
40°-50°	40.0	9.5
50°-60°	8.5	2.0
60°-70°	4.1	1.0
70°-80°	2.5	0.6
80°-90°	0.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	275.7	65.6
0°-40°	363.9	86.7
0°-60°	412.5	98.2
0°-90°	420.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	420.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	452	
5°	446	42
15°	394	109
25°	273	124
35°	140	88
45°	50	40
55°	6	9
65°	4	4
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P1290911

CATALOG NUMBER: P3A05R60W2N902765DE010 E3DLP1WH_6500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	452.3
2.5°	450.7
5°	446.3
7.5°	438.7
10°	428.3
12.5°	413.6
15°	393.6
17.5°	368.4
20°	338.9
22.5°	307.0
25°	273.4
27.5°	239.1
30°	204.8
32.5°	172.0
35°	140.5
37.5°	112.6
40°	87.4
42.5°	66.3
45°	50.3
47.5°	37.5
50°	24.7
52.5°	11.6
55°	6.4
57.5°	5.6
60°	5.2
62.5°	4.8
65°	4.0
67.5°	3.6
70°	3.2
72.5°	2.8
75°	2.4
77.5°	2.0
80°	1.6
82.5°	1.2
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)