

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1304575

Luminaire Tested: P3DUS17R509740DE010 E3CBUS1MW

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1304575  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-91)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3DUS17R509740DE010 E3CBUS1MW  
Description: 3in Adjustable LED luminaire with, R50 optic, 4000K CCT AND, 97CRI , E3CBUS1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1810.0 lumens  
Efficiency: N/A  
Efficacy: 85.4 lumens/watt  
Spacing Criteria (0/90/45): 0.71 / 0.71 / 0.72  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 21.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1304575

CATALOG NUMBER: P3DUS17R509740DE010 E3CBUS1MW

### Luminous Intensity Polar Plot



TEST NUMBER: P1304575

CATALOG NUMBER: P3DUS17R509740DE010 E3CBUS1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 114 | 112 | 110 | 108 | 112 | 110 | 108 | 106 | 106 | 104 | 103 |  | 102 | 101 | 100 |  | 99  |
| 2   | 110 | 105 | 102 | 99  | 108 | 104 | 101 | 98  | 101 | 98  | 96  |  | 98  | 96  | 94  |  | 95  |
| 3   | 105 | 100 | 95  | 92  | 103 | 98  | 94  | 91  | 96  | 93  | 90  |  | 93  | 91  | 89  |  | 91  |
| 4   | 101 | 95  | 90  | 86  | 99  | 93  | 89  | 86  | 91  | 88  | 85  |  | 89  | 86  | 84  |  | 88  |
| 5   | 97  | 90  | 85  | 81  | 95  | 89  | 84  | 81  | 87  | 83  | 80  |  | 86  | 82  | 79  |  | 84  |
| 6   | 93  | 85  | 80  | 77  | 92  | 85  | 80  | 76  | 83  | 79  | 76  |  | 82  | 78  | 75  |  | 81  |
| 7   | 89  | 81  | 76  | 73  | 88  | 81  | 76  | 73  | 80  | 75  | 72  |  | 79  | 75  | 72  |  | 77  |
| 8   | 86  | 78  | 73  | 69  | 85  | 77  | 72  | 69  | 76  | 72  | 69  |  | 75  | 71  | 69  |  | 74  |
| 9   | 83  | 74  | 69  | 66  | 82  | 74  | 69  | 66  | 73  | 69  | 66  |  | 72  | 68  | 65  |  | 71  |
| 10  | 79  | 71  | 66  | 63  | 79  | 71  | 66  | 63  | 70  | 66  | 63  |  | 69  | 65  | 63  |  | 69  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 729744 |
| 5°  | 712259 |
| 10° | 672867 |
| 15° | 591354 |
| 20° | 444842 |
| 25° | 328882 |
| 30° | 199524 |
| 35° | 65959  |
| 40° | 11622  |
| 45° | 0      |
| 50° | 0      |
| 55° | 0      |
| 60° | 0      |
| 65° | 0      |
| 70° | 0      |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 0 cd/sqm

TEST NUMBER: P1304575

CATALOG NUMBER: P3DUS17R509740DE010 E3CBUS1MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 302.1  | 16.7      |
| 10°-20°   | 708.4  | 39.1      |
| 20°-30°   | 607.5  | 33.6      |
| 30°-40°   | 187.3  | 10.4      |
| 40°-50°   | 4.7    | 0.3       |
| 50°-60°   | 0.0    | 0.0       |
| 60°-70°   | 0.0    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 1618.0 | 89.4      |
| 0°-40°    | 1805.3 | 99.7      |
| 0°-60°    | 1810.0 | 100.0     |
| 0°-90°    | 1810.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1810.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 3328 |      |
| 5°  | 3236 | 302  |
| 15° | 2605 | 708  |
| 25° | 1359 | 607  |
| 35° | 246  | 187  |
| 45° | 0    | 5    |
| 55° | 0    | 0    |
| 65° | 0    | 0    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |

TEST NUMBER: P1304575

CATALOG NUMBER: P3DUS17R509740DE010 E3CBUS1MW

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 3327.9 |
| 2.5°  | 3303.5 |
| 5°    | 3235.8 |
| 7.5°  | 3141.0 |
| 10°   | 3021.9 |
| 12.5° | 2832.3 |
| 15°   | 2604.9 |
| 17.5° | 2315.2 |
| 20°   | 1906.3 |
| 22.5° | 1559.7 |
| 25°   | 1359.3 |
| 27.5° | 1104.8 |
| 30°   | 788.0  |
| 32.5° | 479.3  |
| 35°   | 246.4  |
| 37.5° | 111.0  |
| 40°   | 40.6   |
| 42.5° | 5.4    |
| 45°   | 0.0    |
| 47.5° | 0.0    |
| 50°   | 0.0    |
| 52.5° | 0.0    |
| 55°   | 0.0    |
| 57.5° | 0.0    |
| 60°   | 0.0    |
| 62.5° | 0.0    |
| 65°   | 0.0    |
| 67.5° | 0.0    |
| 70°   | 0.0    |
| 72.5° | 0.0    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |

(END OF REPORT)