

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1290914

Luminaire Tested: P3A05R60W2N902765DE010 E3DLP1WMH_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1290914
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R60W2N902765DE010 E3DLP1WMH_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 3500K CCT AND, 90CRI ,
E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 291.9 lumens
Efficiency: N/A
Efficacy: 49.5 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1290914

CATALOG NUMBER: P3A05R60W2N902765DE010 E3DLP1WMH_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1290914

CATALOG NUMBER: P3A05R60W2N902765DE010 E3DLP1WMH_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10		0			
RCR																										
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102		100			
1	113	110	107	105		110	108	105	103		104	102	100		100	98	97		96	95	94		92			
2	107	101	97	93		104	100	96	92		96	93	90		93	91	88		91	88	86		85			
3	101	94	88	84		99	92	87	83		90	86	82		87	84	81		85	82	80		78			
4	95	87	81	77		93	86	80	76		84	79	75		82	78	74		80	76	73		72			
5	90	81	75	70		88	80	74	70		78	73	69		77	72	69		75	71	68		66			
6	85	76	69	65		84	75	69	65		73	68	64		72	67	64		71	67	63		62			
7	81	71	65	60		79	70	64	60		69	64	60		68	63	59		67	62	59		58			
8	77	67	60	56		75	66	60	56		65	60	56		64	59	55		63	58	55		54			
9	73	63	57	52		72	62	56	52		61	56	52		60	55	52		60	55	52		50			
10	69	59	53	49		68	59	53	49		58	53	49		57	52	49		56	52	49		47			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	74007
5°	72331
10°	67734
15°	60772
20°	52248
25°	43212
30°	34132
35°	25350
40°	17461
45°	10947
50°	6038
55°	3517
60°	3158
65°	2698
70°	2308
75°	2372
80°	2020
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10947 cd/sqm

TEST NUMBER: P1290914

CATALOG NUMBER: P3A05R60W2N902765DE010 E3DLP1WMH_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	30.6	10.5
10°-20°	74.3	25.5
20°-30°	81.5	27.9
30°-40°	59.4	20.3
40°-50°	28.1	9.6
50°-60°	9.2	3.1
60°-70°	5.2	1.8
70°-80°	2.8	1.0
80°-90°	0.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	186.5	63.9
0°-40°	245.9	84.2
0°-60°	283.1	97.0
0°-90°	291.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	291.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	338	
5°	329	31
15°	268	74
25°	179	82
35°	95	59
45°	35	28
55°	9	9
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1290914

CATALOG NUMBER: P3A05R60W2N902765DE010 E3DLP1WMH_3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	337.5
2.5°	335.5
5°	328.6
7.5°	318.2
10°	304.2
12.5°	287.3
15°	267.7
17.5°	246.4
20°	223.9
22.5°	201.0
25°	178.6
27.5°	156.1
30°	134.8
32.5°	114.4
35°	94.7
37.5°	77.0
40°	61.0
42.5°	46.9
45°	35.3
47.5°	25.7
50°	17.7
52.5°	11.6
55°	9.2
57.5°	8.0
60°	7.2
62.5°	6.0
65°	5.2
67.5°	4.4
70°	3.6
72.5°	3.2
75°	2.8
77.5°	2.0
80°	1.6
82.5°	1.2
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)