

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1290936

Luminaire Tested: P3A05R65W2N902750DE010 E3CD1MB\_4000K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1290936  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A05R65W2N902750DE010 E3CD1MB\_4000K  
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 4000K CCT AND, 90CRI ,  
E3CD1MB TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 497.0 lumens  
Efficiency: N/A  
Efficacy: 84.2 lumens/watt  
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1290936

CATALOG NUMBER: P3A05R65W2N902750DE010 E3CD1MB\_4000K

### Luminous Intensity Polar Plot



TEST NUMBER: P1290936

CATALOG NUMBER: P3A05R65W2N902750DE010 E3CD1MB\_4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |     |     |  | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 |  | 100 |
| 1   | 114 | 111 | 108 | 106 | 111 | 109 | 106 | 104 | 105 | 103 | 101 |  | 101 | 99  | 98  |  | 97  | 96  | 95  |  | 94  |
| 2   | 108 | 103 | 99  | 96  | 106 | 101 | 98  | 95  | 98  | 95  | 93  |  | 95  | 93  | 91  |  | 92  | 90  | 89  |  | 87  |
| 3   | 103 | 96  | 91  | 87  | 101 | 95  | 90  | 87  | 92  | 88  | 85  |  | 90  | 87  | 84  |  | 88  | 85  | 83  |  | 81  |
| 4   | 97  | 90  | 84  | 80  | 96  | 89  | 84  | 80  | 87  | 82  | 79  |  | 85  | 81  | 78  |  | 83  | 80  | 77  |  | 75  |
| 5   | 93  | 84  | 78  | 74  | 91  | 83  | 78  | 74  | 82  | 77  | 73  |  | 80  | 76  | 73  |  | 78  | 75  | 72  |  | 70  |
| 6   | 88  | 79  | 73  | 69  | 86  | 78  | 73  | 69  | 77  | 72  | 68  |  | 75  | 71  | 68  |  | 74  | 70  | 67  |  | 66  |
| 7   | 84  | 74  | 68  | 64  | 82  | 74  | 68  | 64  | 72  | 67  | 64  |  | 71  | 67  | 63  |  | 70  | 66  | 63  |  | 62  |
| 8   | 80  | 70  | 64  | 60  | 78  | 69  | 64  | 60  | 68  | 63  | 60  |  | 67  | 63  | 59  |  | 66  | 62  | 59  |  | 58  |
| 9   | 76  | 66  | 60  | 56  | 75  | 66  | 60  | 56  | 65  | 60  | 56  |  | 64  | 59  | 56  |  | 63  | 59  | 56  |  | 54  |
| 10  | 72  | 63  | 57  | 53  | 71  | 62  | 57  | 53  | 61  | 56  | 53  |  | 60  | 56  | 53  |  | 60  | 55  | 52  |  | 51  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 121460 |
| 5°  | 114307 |
| 10° | 112868 |
| 15° | 110875 |
| 20° | 104682 |
| 25° | 97143  |
| 30° | 75505  |
| 35° | 43687  |
| 40° | 17604  |
| 45° | 8094   |
| 50° | 3138   |
| 55° | 1223   |
| 60° | 1053   |
| 65° | 1038   |
| 70° | 1026   |
| 75° | 1017   |
| 80° | 1010   |
| 85° | 1006   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 8094 cd/sqm

TEST NUMBER: P1290936

CATALOG NUMBER: P3A05R65W2N902750DE010 E3CD1MB\_4000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 49.4   | 9.9       |
| 10°-20°   | 136.4  | 27.4      |
| 20°-30°   | 178.5  | 35.9      |
| 30°-40°   | 103.4  | 20.8      |
| 40°-50°   | 22.1   | 4.5       |
| 50°-60°   | 3.6    | 0.7       |
| 60°-70°   | 2.0    | 0.4       |
| 70°-80°   | 1.2    | 0.2       |
| 80°-90°   | 0.4    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 364.3  | 73.3      |
| 0°-40°    | 467.7  | 94.1      |
| 0°-60°    | 493.4  | 99.3      |
| 0°-90°    | 497.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 497.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 554 |      |
| 5°  | 519 | 49   |
| 15° | 488 | 136  |
| 25° | 402 | 179  |
| 35° | 163 | 103  |
| 45° | 26  | 22   |
| 55° | 3   | 4    |
| 65° | 2   | 2    |
| 75° | 1   | 1    |
| 85° | 0   | 0    |
| 90° | 0   |      |

TEST NUMBER: P1290936

CATALOG NUMBER: P3A05R65W2N902750DE010 E3CD1MB\_4000K

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 553.9 |
| 2.5°  | 538.2 |
| 5°    | 519.3 |
| 7.5°  | 511.7 |
| 10°   | 506.9 |
| 12.5° | 500.0 |
| 15°   | 488.4 |
| 17.5° | 470.3 |
| 20°   | 448.6 |
| 22.5° | 428.1 |
| 25°   | 401.5 |
| 27.5° | 356.9 |
| 30°   | 298.2 |
| 32.5° | 231.1 |
| 35°   | 163.2 |
| 37.5° | 103.3 |
| 40°   | 61.5  |
| 42.5° | 38.6  |
| 45°   | 26.1  |
| 47.5° | 16.9  |
| 50°   | 9.2   |
| 52.5° | 4.4   |
| 55°   | 3.2   |
| 57.5° | 2.8   |
| 60°   | 2.4   |
| 62.5° | 2.4   |
| 65°   | 2.0   |
| 67.5° | 1.6   |
| 70°   | 1.6   |
| 72.5° | 1.2   |
| 75°   | 1.2   |
| 77.5° | 0.8   |
| 80°   | 0.8   |
| 82.5° | 0.4   |
| 85°   | 0.4   |
| 87.5° | 0.4   |
| 90°   | 0.0   |

(END OF REPORT)