

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1304671

Luminaire Tested: P3DUS05R559830DE010 E3CBUS1MW

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1304671  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-92)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3DUS05R559830DE010 E3CBUS1MW  
Description: 3in Adjustable LED luminaire with, R55 optic, 3000K CCT AND, 98CRI , E3CBUS1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 530.0 lumens  
Efficiency: N/A  
Efficacy: 73.6 lumens/watt  
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.77  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1304671  
CATALOG NUMBER: P3DUS05R559830DE010 E3CBUS1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1304671  
 CATALOG NUMBER: P3DUS05R559830DE010 E3CBUS1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20					
RC	80				70				50				30				10			0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	98	98	97	95
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	98	98	97	95	95	93	91	90
2	109	105	102	99	107	103	100	97	100	98	95	97	95	93	95	93	91	90	91	88	87	85
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	87	85	87	84	82	81
4	100	94	89	85	99	93	88	85	91	87	84	89	86	83	87	84	82	81	83	80	78	76
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76	83	80	78	76
6	92	84	79	76	91	84	79	75	82	78	75	81	77	74	80	76	74	73	80	76	74	73
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69	76	73	70	69
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65	73	69	67	65
9	81	73	68	64	80	72	67	64	72	67	64	71	67	64	70	66	64	62	70	66	64	62
10	78	70	64	61	77	69	64	61	68	64	61	68	64	61	67	63	61	59	67	63	61	59

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	176104
5°	168104
10°	168089
15°	162793
20°	147293
25°	114055
30°	57148
35°	17186
40°	3664
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 0 cd/sqm



TEST NUMBER: P1304671  
 CATALOG NUMBER: P3DUS05R559830DE010 E3CBUS1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	72.9	13.8
10°-20°	198.9	37.5
20°-30°	204.8	38.6
30°-40°	51.6	9.7
40°-50°	1.7	0.3
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	476.6	89.9
0°-40°	528.2	99.7
0°-60°	530.0	100.0
0°-90°	530.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	530.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	803	
5°	764	73
15°	717	199
25°	471	205
35°	64	52
45°	0	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1304671  
CATALOG NUMBER: P3DUS05R559830DE010 E3CBUS1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	803.1
2.5°	787.0
5°	763.7
7.5°	758.9
10°	754.9
12.5°	740.4
15°	717.1
17.5°	681.0
20°	631.2
22.5°	563.7
25°	471.4
27.5°	354.1
30°	225.7
32.5°	130.9
35°	64.2
37.5°	30.5
40°	12.8
42.5°	3.2
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)