

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1304763

Luminaire Tested: P3DUS17R359835DE010 E3CBUS1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1304763
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-89)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3DUS17R359835DE010 E3CBUS1MW
Description: 3in Adjustable LED luminaire with, R35 optic, 3500K CCT AND, 98CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1711.0 lumens
Efficiency: N/A
Efficacy: 83.9 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 0.55 / 0.5
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1304763
CATALOG NUMBER: P3DUS17R359835DE010 E3CBUS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1304763
 CATALOG NUMBER: P3DUS17R359835DE010 E3CBUS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	100
1	115	113	111	109	113	111	109	108	107	105	104	103	102	101	100	99	98	97	96	95	97
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	94	93	92	93
3	108	103	99	97	106	102	98	96	99	97	94	97	95	93	95	93	92	91	90	89	90
4	104	99	95	92	103	98	94	92	96	93	90	94	92	89	92	90	89	88	87	86	87
5	101	95	91	88	100	94	91	88	93	90	87	91	89	86	90	88	86	85	84	83	85
6	98	92	88	85	97	91	87	85	90	87	84	89	86	83	88	85	83	82	81	80	82
7	95	89	85	82	94	88	84	82	87	84	81	86	83	81	85	83	80	79	78	77	79
8	93	86	82	79	92	86	82	79	85	81	79	84	81	78	83	80	78	77	76	75	77
9	90	83	79	77	89	83	79	76	82	79	76	82	78	76	81	78	76	75	74	73	75
10	88	81	77	74	87	81	77	74	80	76	74	79	76	74	79	76	74	73	72	71	73

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1253408
5°	1216021
10°	1084326
15°	766020
20°	369492
25°	119765
30°	33701
35°	13545
40°	3807
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 0 cd/sqm



TEST NUMBER: P1304763
 CATALOG NUMBER: P3DUS17R359835DE010 E3CBUS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	507.3	29.7
10°-20°	891.8	52.1
20°-30°	274.1	16.0
30°-40°	35.6	2.1
40°-50°	2.2	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1673.2	97.8
0°-40°	1708.8	99.9
0°-60°	1711.0	100.0
0°-90°	1711.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1711.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5716	
5°	5524	507
15°	3374	892
25°	495	274
35°	51	36
45°	0	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1304763
CATALOG NUMBER: P3DUS17R359835DE010 E3CBUS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	5716.0
2.5°	5670.8
5°	5524.4
7.5°	5282.3
10°	4869.8
12.5°	4225.8
15°	3374.3
17.5°	2448.2
20°	1583.4
22.5°	918.1
25°	495.0
27.5°	260.8
30°	133.1
32.5°	79.8
35°	50.6
37.5°	31.9
40°	13.3
42.5°	5.3
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)