

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1304767

Luminaire Tested: P3DUS17R559835DE010 E3CBUS1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1304767
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-92)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3DUS17R559835DE010 E3CBUS1MW
Description: 3in Adjustable LED luminaire with, R55 optic, 3500K CCT AND, 98CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1757.0 lumens
Efficiency: N/A
Efficacy: 86.1 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1304767
CATALOG NUMBER: P3DUS17R559835DE010 E3CBUS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1304767
 CATALOG NUMBER: P3DUS17R559835DE010 E3CBUS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	98	98	97	98	98	97	95
2	109	105	102	99	107	103	100	97	100	98	95	97	95	93	95	93	91	95	93	91	90
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	87	91	88	87	85
4	100	94	89	85	99	93	88	85	91	87	84	89	86	83	87	84	82	87	84	82	81
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	83	80	78	76
6	92	84	79	76	91	84	79	75	82	78	75	81	77	74	80	76	74	80	76	74	73
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	76	73	70	69
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	73	69	67	65
9	81	73	68	64	80	72	67	64	72	67	64	71	67	64	70	66	64	70	66	64	62
10	78	70	64	61	77	69	64	61	68	64	61	68	64	61	67	63	61	67	63	61	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	583769
5°	557295
10°	557215
15°	539708
20°	488292
25°	378094
30°	189422
35°	57018
40°	12194
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 0 cd/sqm



TEST NUMBER: P1304767
 CATALOG NUMBER: P3DUS17R559835DE010 E3CBUS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	241.8	13.8
10°-20°	659.4	37.5
20°-30°	678.9	38.6
30°-40°	171.1	9.7
40°-50°	5.8	0.3
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1580.1	89.9
0°-40°	1751.2	99.7
0°-60°	1757.0	100.0
0°-90°	1757.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1757.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2662	
5°	2532	242
15°	2377	659
25°	1563	679
35°	213	171
45°	0	6
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1304767
CATALOG NUMBER: P3DUS17R559835DE010 E3CBUS1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	2662.2
2.5°	2609.0
5°	2531.8
7.5°	2515.8
10°	2502.5
12.5°	2454.6
15°	2377.4
17.5°	2257.6
20°	2092.5
22.5°	1868.9
25°	1562.7
27.5°	1174.0
30°	748.1
32.5°	433.9
35°	213.0
37.5°	101.2
40°	42.6
42.5°	10.6
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)