

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1304768

Luminaire Tested: P3DUS17R609835DE010 E3CBUS1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1304768
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-93)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3DUS17R609835DE010 E3CBUS1MW
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 98CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1680.0 lumens
Efficiency: N/A
Efficacy: 82.4 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.84
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1304768

CATALOG NUMBER: P3DUS17R609835DE010 E3CBUS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1304768

CATALOG NUMBER: P3DUS17R609835DE010 E3CBUS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94	92	90	89
3	104	98	93	89	102	96	92	89	94	90	87		91	88	86		89	87	85	83
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85	82	79	78
5	94	86	81	77	93	86	80	77	84	79	76		82	78	75		81	77	75	73
6	90	82	76	72	89	81	76	72	79	75	71		78	74	71		77	73	70	69
7	86	77	71	68	85	76	71	67	75	70	67		74	70	67		73	69	66	65
8	82	73	67	63	81	72	67	63	71	67	63		70	66	63		69	66	63	61
9	78	69	64	60	77	69	63	60	68	63	60		67	63	59		66	62	59	58
10	75	66	60	57	74	65	60	56	64	60	56		64	59	56		63	59	56	55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	473164
5°	459167
10°	463296
15°	446972
20°	378126
25°	307082
30°	227048
35°	157403
40°	56363
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 0 cd/sqm

TEST NUMBER: P1304768

CATALOG NUMBER: P3DUS17R609835DE010 E3CBUS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	199.3	11.9
10°-20°	538.2	32.0
20°-30°	573.4	34.1
30°-40°	348.3	20.7
40°-50°	20.8	1.2
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1311.0	78.0
0°-40°	1659.2	98.8
0°-60°	1680.0	100.0
0°-90°	1680.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1680.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2158	
5°	2086	199
15°	1969	538
25°	1269	573
35°	588	348
45°	0	21
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1304768

CATALOG NUMBER: P3DUS17R609835DE010 E3CBUS1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	2157.8
2.5°	2125.9
5°	2086.0
7.5°	2075.4
10°	2080.7
12.5°	2056.7
15°	1968.9
17.5°	1814.6
20°	1620.4
22.5°	1434.1
25°	1269.2
27.5°	1077.6
30°	896.7
32.5°	755.6
35°	588.0
37.5°	383.1
40°	196.9
42.5°	16.0
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)