

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1291120

Luminaire Tested: P3A05R65W2N902765DE010 E3D1WH_4000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1291120
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R65W2N902765DE010 E3D1WH_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 4000K CCT AND, 90CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 479.0 lumens
Efficiency: N/A
Efficacy: 81.2 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1291120

CATALOG NUMBER: P3A05R65W2N902765DE010 E3D1WH_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1291120

CATALOG NUMBER: P3A05R65W2N902765DE010 E3D1WH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	109	106		111	109	107	105		105	103	102		101	100	99		98	97	96
2	108	104	100	96		106	102	98	95		99	96	93		96	93	91		93	91	89
3	103	97	92	88		101	95	91	88		93	89	86		90	87	85		88	86	83
4	98	91	85	81		96	90	85	81		87	83	80		85	82	79		84	81	78
5	93	85	79	75		92	84	79	75		82	78	74		81	77	74		79	76	73
6	89	80	74	70		87	79	74	70		78	73	69		76	72	69		75	71	68
7	84	75	70	65		83	75	69	65		73	69	65		72	68	65		71	67	64
8	80	71	65	61		79	71	65	61		69	64	61		68	64	61		67	63	60
9	77	67	61	58		76	67	61	57		66	61	57		65	60	57		64	60	57
10	73	64	58	54		72	63	58	54		62	57	54		62	57	54		61	57	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	128345
5°	119172
10°	115251
15°	111056
20°	102676
25°	93562
30°	72290
35°	41894
40°	16631
45°	7071
50°	1672
55°	229
60°	175
65°	104
70°	128
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 7071 cd/sqm

TEST NUMBER: P1291120

CATALOG NUMBER: P3A05R65W2N902765DE010 E3D1WH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.1	10.7
10°-20°	136.3	28.5
20°-30°	172.5	36.0
30°-40°	98.3	20.5
40°-50°	19.5	4.1
50°-60°	1.0	0.2
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	359.9	75.1
0°-40°	458.2	95.7
0°-60°	478.7	99.9
0°-90°	479.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	479.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	585	
5°	541	51
15°	489	136
25°	387	173
35°	156	98
45°	23	20
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1291120

CATALOG NUMBER: P3A05R65W2N902765DE010 E3D1WH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	585.3
1°	581.0
2°	571.5
3°	560.5
4°	549.7
5°	541.4
6°	535.3
7°	530.4
8°	526.1
9°	521.7
10°	517.6
11°	513.1
12°	508.3
13°	502.6
14°	496.5
15°	489.2
16°	480.6
17°	471.1
18°	460.9
19°	450.1
20°	440.0
21°	429.8
22°	420.5
23°	410.9
24°	399.7
25°	386.7
26°	371.1
27°	352.4
28°	331.4
29°	308.9
30°	285.5
31°	259.7
32°	234.1
32.5°	220.9
33°	208.1
34°	182.1
35°	156.5
36°	132.9
37°	109.5
37.5°	97.5
38°	87.8
39°	71.1
40°	58.1
42.5°	35.8
45°	22.8



TEST NUMBER: P1291120

CATALOG NUMBER: P3A05R65W2N902765DE010 E3D1WH_4000K

CANDELA DISTRIBUTION (continued):

	0°
47.5°	13.4
50°	4.9
52.5°	1.0
55°	0.6
57.5°	0.4
60°	0.4
62.5°	0.4
65°	0.2
67.5°	0.2
70°	0.2
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)