

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1304824

Luminaire Tested: P3DUS17R409840DE010 E3CBUS1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1304824
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-90)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3DUS17R409840DE010 E3CBUS1MW
Description: 3in Adjustable LED luminaire with, R40 optic, 4000K CCT AND, 98CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1831.0 lumens
Efficiency: N/A
Efficacy: 89.8 lumens/watt
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.55
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1304824
CATALOG NUMBER: P3DUS17R409840DE010 E3CBUS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1304824
 CATALOG NUMBER: P3DUS17R409840DE010 E3CBUS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	100
1	115	113	111	109	113	111	109	107	107	105	104	103	102	101	100	99	98	97	96	94	96
2	111	107	104	102	109	106	103	101	103	100	98	100	98	96	97	96	94	94	93	91	93
3	107	103	99	96	106	101	98	95	99	96	94	97	94	92	94	93	91	92	90	88	90
4	104	98	94	91	102	97	94	91	95	92	90	94	91	89	92	90	88	89	87	85	87
5	101	95	90	87	99	94	90	87	92	89	86	91	88	86	89	87	85	87	84	82	84
6	98	91	87	84	96	90	86	84	89	86	83	88	85	83	87	84	82	84	81	79	81
7	95	88	84	81	94	87	83	80	86	83	80	85	82	80	84	81	79	82	79	77	79
8	92	85	81	78	91	85	80	78	84	80	77	83	79	77	82	79	77	80	77	74	77
9	89	82	78	75	88	82	78	75	81	77	75	80	77	75	80	77	74	80	77	74	73
10	87	80	76	73	86	79	75	73	79	75	73	78	75	72	77	74	72	77	74	72	71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1125765
5°	1115163
10°	1048567
15°	863978
20°	478445
25°	138734
30°	34233
35°	12314
40°	3092
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 0 cd/sqm



TEST NUMBER: P1304824

CATALOG NUMBER: P3DUS17R409840DE010 E3CBUS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	472.6	25.8
10°-20°	996.1	54.4
20°-30°	327.8	17.9
30°-40°	33.0	1.8
40°-50°	1.5	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1796.5	98.1
0°-40°	1829.5	99.9
0°-60°	1831.0	100.0
0°-90°	1831.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1831.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5134	
5°	5066	473
15°	3806	996
25°	573	328
35°	46	33
45°	0	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1304824
CATALOG NUMBER: P3DUS17R409840DE010 E3CBUS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	5133.9
2.5°	5125.7
5°	5066.2
7.5°	4941.8
10°	4709.2
12.5°	4349.4
15°	3805.8
17.5°	3056.5
20°	2050.3
22.5°	1106.3
25°	573.4
27.5°	273.2
30°	135.2
32.5°	75.7
35°	46.0
37.5°	24.3
40°	10.8
42.5°	2.7
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)