

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1291217

Luminaire Tested: P3A05R65W2N902765DE010 E3DLP1LI\_5000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1291217  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A05R65W2N902765DE010 E3DLP1LI\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 5000K CCT AND, 90CRI ,  
E3DLP1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 277.0 lumens  
Efficiency: N/A  
Efficacy: 47.0 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1291217  
CATALOG NUMBER: P3A05R65W2N902765DE010 E3DLP1LI\_5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1291217  
 CATALOG NUMBER: P3A05R65W2N902765DE010 E3DLP1LI\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |    |    |   |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |    | 0  |   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |   |
| 1   | 113 | 110 | 107 | 105 | 110 | 108 | 105 | 103 | 104 | 102 | 100 | 100 | 98  | 97  | 96  | 95  | 94  | 92  |    |    |   |
| 2   | 107 | 101 | 97  | 93  | 104 | 100 | 96  | 92  | 96  | 93  | 90  | 93  | 91  | 88  | 90  | 88  | 86  | 85  |    |    |   |
| 3   | 101 | 94  | 88  | 84  | 99  | 92  | 87  | 83  | 90  | 85  | 82  | 87  | 84  | 81  | 85  | 82  | 79  | 78  |    |    |   |
| 4   | 95  | 87  | 81  | 76  | 93  | 86  | 80  | 76  | 84  | 79  | 75  | 82  | 78  | 74  | 80  | 76  | 73  | 72  |    |    |   |
| 5   | 90  | 81  | 75  | 70  | 88  | 80  | 74  | 70  | 78  | 73  | 69  | 77  | 72  | 69  | 75  | 71  | 68  | 66  |    |    |   |
| 6   | 85  | 76  | 69  | 65  | 84  | 75  | 69  | 65  | 73  | 68  | 64  | 72  | 67  | 64  | 71  | 66  | 63  | 62  |    |    |   |
| 7   | 81  | 71  | 65  | 60  | 79  | 70  | 64  | 60  | 69  | 64  | 60  | 68  | 63  | 59  | 67  | 62  | 59  | 57  |    |    |   |
| 8   | 77  | 67  | 60  | 56  | 75  | 66  | 60  | 56  | 65  | 59  | 56  | 64  | 59  | 55  | 63  | 58  | 55  | 54  |    |    |   |
| 9   | 73  | 63  | 57  | 52  | 72  | 62  | 56  | 52  | 61  | 56  | 52  | 60  | 55  | 52  | 59  | 55  | 52  | 50  |    |    |   |
| 10  | 69  | 59  | 53  | 49  | 68  | 59  | 53  | 49  | 58  | 53  | 49  | 57  | 52  | 49  | 56  | 52  | 49  | 47  |    |    |   |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 70411 |
| 5°  | 68655 |
| 10° | 63927 |
| 15° | 57299 |
| 20° | 49494 |
| 25° | 41156 |
| 30° | 32461 |
| 35° | 24066 |
| 40° | 16574 |
| 45° | 10265 |
| 50° | 5595  |
| 55° | 3517  |
| 60° | 2982  |
| 65° | 2698  |
| 70° | 2308  |
| 75° | 2033  |
| 80° | 2020  |
| 85° | 2013  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 10265 cd/sqm



TEST NUMBER: P1291217

CATALOG NUMBER: P3A05R65W2N902765DE010 E3DLP1LI\_5000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 29.0   | 10.5      |
| 10°-20°   | 70.1   | 25.3      |
| 20°-30°   | 77.6   | 28.0      |
| 30°-40°   | 56.3   | 20.3      |
| 40°-50°   | 26.4   | 9.5       |
| 50°-60°   | 8.9    | 3.2       |
| 60°-70°   | 5.1    | 1.9       |
| 70°-80°   | 2.7    | 1.0       |
| 80°-90°   | 0.9    | 0.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 176.7  | 63.8      |
| 0°-40°    | 233.0  | 84.1      |
| 0°-60°    | 268.3  | 96.9      |
| 0°-90°    | 277.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 277.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 321 |      |
| 5°  | 312 | 29   |
| 15° | 252 | 70   |
| 25° | 170 | 78   |
| 35° | 90  | 56   |
| 45° | 33  | 26   |
| 55° | 9   | 9    |
| 65° | 5   | 5    |
| 75° | 2   | 3    |
| 85° | 1   | 1    |
| 90° | 0   |      |



TEST NUMBER: P1291217  
CATALOG NUMBER: P3A05R65W2N902765DE010 E3DLP1LI\_5000K

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 321.1 |
| 2.5°  | 319.1 |
| 5°    | 311.9 |
| 7.5°  | 301.1 |
| 10°   | 287.1 |
| 12.5° | 270.8 |
| 15°   | 252.4 |
| 17.5° | 232.4 |
| 20°   | 212.1 |
| 22.5° | 190.9 |
| 25°   | 170.1 |
| 27.5° | 149.0 |
| 30°   | 128.2 |
| 32.5° | 108.2 |
| 35°   | 89.9  |
| 37.5° | 73.1  |
| 40°   | 57.9  |
| 42.5° | 44.3  |
| 45°   | 33.1  |
| 47.5° | 24.0  |
| 50°   | 16.4  |
| 52.5° | 11.2  |
| 55°   | 9.2   |
| 57.5° | 8.0   |
| 60°   | 6.8   |
| 62.5° | 6.0   |
| 65°   | 5.2   |
| 67.5° | 4.4   |
| 70°   | 3.6   |
| 72.5° | 3.2   |
| 75°   | 2.4   |
| 77.5° | 2.0   |
| 80°   | 1.6   |
| 82.5° | 1.2   |
| 85°   | 0.8   |
| 87.5° | 0.4   |
| 90°   | 0.0   |

(END OF REPORT)