

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1304861

Luminaire Tested: P3DUS02R30B2750DE010 E3CBUS1MW_4000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1304861
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-88)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3DUS02R30B2750DE010 E3CBUS1MW_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R30 optic, 4000K CCT AND, 80CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 281.0 lumens
Efficiency: N/A
Efficacy: 96.9 lumens/watt
Spacing Criteria (0/90/45): 0.5 / 0.5 / 0.45
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 2.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1304861

CATALOG NUMBER: P3DUS02R30B2750DE010 E3CBUS1MW_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1304861

CATALOG NUMBER: P3DUS02R30B2750DE010 E3CBUS1MW_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20				20				20
RC	80				70				50				30				10				0				0				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99	97	97	97	94	94	94	92	92	92
1	115	113	111	110	113	111	109	108	107	106	105	103	103	102	100	99	99	97	97	96	94	94	94	92	92	92	90	90	90
2	112	108	105	103	110	107	104	102	104	101	100	101	99	98	98	97	96	94	94	93	92	92	92	90	90	90	88	88	88
3	108	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92	92	90	89	89	87	87	87	85	85	85	85
4	105	100	97	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89	88	87	86	86	84	84	84	82	82	82	82
5	102	97	93	90	101	96	93	90	95	91	89	93	90	88	92	89	88	87	86	85	84	84	82	82	82	80	80	80	80
6	100	94	90	87	99	93	90	87	92	89	86	91	88	86	90	87	85	84	83	82	82	80	80	80	78	78	78	78	78
7	97	91	87	84	96	91	87	84	90	86	84	89	86	83	88	85	83	82	81	81	80	80	79	79	79	77	77	77	77
8	95	89	85	82	94	88	84	82	87	84	82	86	83	81	86	83	81	80	79	79	78	78	77	77	76	76	76	76	76
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78	77	77	76	76	75	75	75	73	73	73	73
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76	75	75	74	74	74	73	73	73	71	71	71

AVERAGE LUMINANCE (cd/sqm):

0°	252063
5°	244904
10°	207277
15°	124836
20°	44967
25°	12630
30°	3342
35°	1285
40°	515
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 0 cd/sqm

TEST NUMBER: P1304861

CATALOG NUMBER: P3DUS02R30B2750DE010 E3CBUS1MW_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.7	35.8
10°-20°	146.3	52.1
20°-30°	30.2	10.8
30°-40°	3.5	1.3
40°-50°	0.2	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	277.2	98.7
0°-40°	280.8	99.9
0°-60°	281.0	100.0
0°-90°	281.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	281.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1150	
5°	1113	101
15°	550	146
25°	52	30
35°	5	4
45°	0	0
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1304861

CATALOG NUMBER: P3DUS02R30B2750DE010 E3CBUS1MW_4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1149.5
2.5°	1140.3
5°	1112.6
7.5°	1051.6
10°	930.9
12.5°	757.5
15°	549.9
17.5°	352.0
20°	192.7
22.5°	96.6
25°	52.2
27.5°	28.5
30°	13.2
32.5°	7.9
35°	4.8
37.5°	3.1
40°	1.8
42.5°	0.4
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)