

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1291383

Luminaire Tested: P3A05R70W2N902765DE010 E3CD1MB\_4000K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1291383  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A05R70W2N902765DE010 E3CD1MB\_4000K  
Description: 3in Adjustable Tunable White LED luminaire with, R70 optic, 4000K CCT AND, 90CRI ,  
E3CD1MB TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 502.0 lumens  
Efficiency: N/A  
Efficacy: 85.1 lumens/watt  
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1291383

CATALOG NUMBER: P3A05R70W2N902765DE010 E3CD1MB\_4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1291383

CATALOG NUMBER: P3A05R70W2N902765DE010 E3CD1MB\_4000K

### COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

|     |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |  |     |  |  |   |
|-----|-----|-----|-----|-----|--|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|--|--|---|
| RF  | 20  |     |     |     |  | 20  |     |     |     |  | 20  |     |     |  |     | 20  |     |  |     |     | 20  |  |     |  |  |   |
| RC  | 80  |     |     |     |  | 70  |     |     |     |  | 50  |     |     |  |     | 30  |     |  |     |     | 10  |  |     |  |  | 0 |
| RW  | 70  | 50  | 30  | 10  |  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 0   |  |  |   |
| RCR |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |  |     |  |  |   |
| 0   | 119 | 119 | 119 | 119 |  | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 |  | 100 |  |  |   |
| 1   | 113 | 110 | 107 | 105 |  | 111 | 108 | 106 | 103 |  | 104 | 102 | 100 |  | 100 | 99  | 97  |  | 97  | 96  | 94  |  | 93  |  |  |   |
| 2   | 107 | 102 | 97  | 94  |  | 105 | 100 | 96  | 93  |  | 97  | 94  | 91  |  | 94  | 91  | 89  |  | 91  | 89  | 87  |  | 85  |  |  |   |
| 3   | 101 | 94  | 89  | 85  |  | 99  | 93  | 88  | 84  |  | 90  | 86  | 83  |  | 88  | 84  | 81  |  | 85  | 82  | 80  |  | 78  |  |  |   |
| 4   | 95  | 87  | 81  | 77  |  | 94  | 86  | 81  | 76  |  | 84  | 79  | 75  |  | 82  | 78  | 75  |  | 80  | 77  | 74  |  | 72  |  |  |   |
| 5   | 90  | 81  | 75  | 70  |  | 88  | 80  | 74  | 70  |  | 78  | 73  | 69  |  | 77  | 72  | 69  |  | 75  | 71  | 68  |  | 66  |  |  |   |
| 6   | 85  | 75  | 69  | 64  |  | 83  | 75  | 69  | 64  |  | 73  | 68  | 64  |  | 72  | 67  | 63  |  | 70  | 66  | 63  |  | 61  |  |  |   |
| 7   | 80  | 70  | 64  | 59  |  | 79  | 70  | 64  | 59  |  | 68  | 63  | 59  |  | 67  | 62  | 59  |  | 66  | 62  | 58  |  | 57  |  |  |   |
| 8   | 76  | 66  | 59  | 55  |  | 75  | 65  | 59  | 55  |  | 64  | 58  | 55  |  | 63  | 58  | 54  |  | 62  | 57  | 54  |  | 53  |  |  |   |
| 9   | 72  | 62  | 55  | 51  |  | 71  | 61  | 55  | 51  |  | 60  | 55  | 51  |  | 59  | 54  | 50  |  | 58  | 54  | 50  |  | 49  |  |  |   |
| 10  | 68  | 58  | 52  | 47  |  | 67  | 57  | 51  | 47  |  | 56  | 51  | 47  |  | 56  | 51  | 47  |  | 55  | 50  | 47  |  | 46  |  |  |   |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°    |
|-----|-------|
| 0°  | 99685 |
| 5°  | 95113 |
| 10° | 90490 |
| 15° | 88082 |
| 20° | 84824 |
| 25° | 80279 |
| 30° | 74670 |
| 35° | 62720 |
| 40° | 40419 |
| 45° | 18793 |
| 50° | 4912  |
| 55° | 1223  |
| 60° | 1228  |
| 65° | 1038  |
| 70° | 1026  |
| 75° | 1017  |
| 80° | 1010  |
| 85° | 1006  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle:  $45^\circ$

Luminance: 18793 cd/sqm

TEST NUMBER: P1291383

CATALOG NUMBER: P3A05R70W2N902765DE010 E3CD1MB\_4000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 40.5   | 8.1       |
| 10°-20°   | 109.0  | 21.7      |
| 20°-30°   | 152.3  | 30.3      |
| 30°-40°   | 141.2  | 28.1      |
| 40°-50°   | 50.6   | 10.1      |
| 50°-60°   | 4.3    | 0.9       |
| 60°-70°   | 2.1    | 0.4       |
| 70°-80°   | 1.4    | 0.3       |
| 80°-90°   | 0.5    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 301.8  | 60.1      |
| 0°-40°    | 443.0  | 88.3      |
| 0°-60°    | 497.9  | 99.2      |
| 0°-90°    | 502.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 502.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 455 |      |
| 5°  | 432 | 40   |
| 15° | 388 | 109  |
| 25° | 332 | 152  |
| 35° | 234 | 141  |
| 45° | 61  | 51   |
| 55° | 3   | 4    |
| 65° | 2   | 2    |
| 75° | 1   | 1    |
| 85° | 0   | 1    |
| 90° | 0   |      |

TEST NUMBER: P1291383

CATALOG NUMBER: P3A05R70W2N902765DE010 E3CD1MB\_4000K

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 454.6 |
| 2.5°  | 447.8 |
| 5°    | 432.1 |
| 7.5°  | 417.7 |
| 10°   | 406.4 |
| 12.5° | 397.2 |
| 15°   | 388.0 |
| 17.5° | 376.8 |
| 20°   | 363.5 |
| 22.5° | 348.3 |
| 25°   | 331.8 |
| 27.5° | 315.0 |
| 30°   | 294.9 |
| 32.5° | 269.2 |
| 35°   | 234.3 |
| 37.5° | 189.8 |
| 40°   | 141.2 |
| 42.5° | 96.3  |
| 45°   | 60.6  |
| 47.5° | 33.7  |
| 50°   | 14.4  |
| 52.5° | 4.8   |
| 55°   | 3.2   |
| 57.5° | 2.8   |
| 60°   | 2.8   |
| 62.5° | 2.4   |
| 65°   | 2.0   |
| 67.5° | 2.0   |
| 70°   | 1.6   |
| 72.5° | 1.6   |
| 75°   | 1.2   |
| 77.5° | 1.2   |
| 80°   | 0.8   |
| 82.5° | 0.8   |
| 85°   | 0.4   |
| 87.5° | 0.4   |
| 90°   | 0.0   |

(END OF REPORT)