

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1291560

Luminaire Tested: P3A09R15W2N902750DE010 E3D1WH\_4000K

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1291560  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-7)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A09R15W2N902750DE010 E3D1WH\_4000K  
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 4000K CCT AND, 90CRI ,  
E3D1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 765.0 lumens  
Efficiency: N/A  
Efficacy: 85.0 lumens/watt  
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1291560

CATALOG NUMBER: P3A09R15W2N902750DE010 E3D1WH\_4000K

### Luminous Intensity Polar Plot



TEST NUMBER: P1291560

CATALOG NUMBER: P3A09R15W2N902750DE010 E3D1WH\_4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |    | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |    | 10 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |
| 1   | 116 | 114 | 112 | 111 | 113 | 112 | 110 | 109 | 108 | 107 | 105 | 104 | 103 | 102 | 101 | 100 | 99  | 98  |    |    |
| 2   | 112 | 109 | 107 | 105 | 110 | 108 | 105 | 103 | 105 | 103 | 101 | 102 | 100 | 99  | 99  | 98  | 97  | 96  |    |    |
| 3   | 110 | 106 | 102 | 100 | 108 | 104 | 102 | 99  | 102 | 100 | 98  | 100 | 98  | 96  | 98  | 96  | 95  | 94  |    |    |
| 4   | 107 | 102 | 99  | 96  | 105 | 101 | 98  | 96  | 99  | 97  | 95  | 98  | 96  | 94  | 96  | 94  | 93  | 92  |    |    |
| 5   | 105 | 100 | 96  | 94  | 103 | 99  | 96  | 93  | 97  | 94  | 92  | 96  | 93  | 92  | 94  | 93  | 91  | 90  |    |    |
| 6   | 102 | 97  | 94  | 91  | 101 | 96  | 93  | 91  | 95  | 92  | 90  | 94  | 92  | 90  | 93  | 91  | 89  | 88  |    |    |
| 7   | 100 | 95  | 91  | 89  | 99  | 94  | 91  | 89  | 93  | 90  | 88  | 92  | 90  | 88  | 91  | 89  | 88  | 87  |    |    |
| 8   | 98  | 93  | 89  | 87  | 97  | 92  | 89  | 87  | 91  | 89  | 87  | 91  | 88  | 86  | 90  | 88  | 86  | 85  |    |    |
| 9   | 96  | 91  | 88  | 85  | 96  | 91  | 87  | 85  | 90  | 87  | 85  | 89  | 87  | 85  | 88  | 86  | 85  | 84  |    |    |
| 10  | 95  | 89  | 86  | 84  | 94  | 89  | 86  | 84  | 88  | 85  | 83  | 88  | 85  | 83  | 87  | 85  | 83  | 82  |    |    |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 1456747 |
| 5°  | 1187890 |
| 10° | 581753  |
| 15° | 178071  |
| 20° | 75397   |
| 25° | 34115   |
| 30° | 13293   |
| 35° | 6130    |
| 40° | 1918    |
| 45° | 713     |
| 50° | 307     |
| 55° | 115     |
| 60° | 132     |
| 65° | 156     |
| 70° | 0       |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 713 cd/sqm

TEST NUMBER: P1291560

CATALOG NUMBER: P3A09R15W2N902750DE010 E3D1WH\_4000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 420.1  | 54.9      |
| 10°-20°   | 257.8  | 33.7      |
| 20°-30°   | 69.2   | 9.0       |
| 30°-40°   | 15.3   | 2.0       |
| 40°-50°   | 2.2    | 0.3       |
| 50°-60°   | 0.4    | 0.1       |
| 60°-70°   | 0.2    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 747.1  | 97.6      |
| 0°-40°    | 762.3  | 99.6      |
| 0°-60°    | 764.9  | 100.0     |
| 0°-90°    | 765.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 765.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 6643 |      |
| 5°  | 5397 | 420  |
| 15° | 784  | 258  |
| 25° | 141  | 69   |
| 35° | 23   | 15   |
| 45° | 2    | 2    |
| 55° | 0    | 0    |
| 65° | 0    | 0    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |

TEST NUMBER: P1291560

CATALOG NUMBER: P3A09R15W2N902750DE010 E3D1WH\_4000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 6643.3 |
| 1°    | 6601.9 |
| 2°    | 6468.7 |
| 3°    | 6228.8 |
| 4°    | 5867.7 |
| 5°    | 5396.6 |
| 6°    | 4863.7 |
| 7°    | 4270.2 |
| 8°    | 3724.9 |
| 9°    | 3146.8 |
| 10°   | 2612.7 |
| 11°   | 2084.2 |
| 12°   | 1603.5 |
| 13°   | 1233.4 |
| 14°   | 976.4  |
| 15°   | 784.4  |
| 17.5° | 486.2  |
| 20°   | 323.1  |
| 22.5° | 217.6  |
| 25°   | 141.0  |
| 27.5° | 83.5   |
| 30°   | 52.5   |
| 32.5° | 35.4   |
| 35°   | 22.9   |
| 37.5° | 12.8   |
| 40°   | 6.7    |
| 42.5° | 3.8    |
| 45°   | 2.3    |
| 47.5° | 1.5    |
| 50°   | 0.9    |
| 52.5° | 0.6    |
| 55°   | 0.3    |
| 57.5° | 0.3    |
| 60°   | 0.3    |
| 62.5° | 0.3    |
| 65°   | 0.3    |
| 67.5° | 0.0    |
| 70°   | 0.0    |
| 72.5° | 0.0    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |



TEST NUMBER: P1291560  
CATALOG NUMBER: P3A09R15W2N902750DE010 E3D1WH\_4000K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)