

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1304931

Luminaire Tested: P3DUS05R40B2750DE010 E3CBUS1MW_4000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1304931
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-90)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3DUS05R40B2750DE010 E3CBUS1MW_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R40 optic, 4000K CCT AND, 80CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 585.0 lumens
Efficiency: N/A
Efficacy: 99.2 lumens/watt
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.55
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1304931

CATALOG NUMBER: P3DUS05R40B2750DE010 E3CBUS1MW_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1304931

CATALOG NUMBER: P3DUS05R40B2750DE010 E3CBUS1MW_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98
1	115	113	111	109	113	111	109	107	107	105	104	103	102	101	100	99	98	97	96	94
2	111	107	104	102	109	106	103	101	103	100	98	100	98	96	97	96	94	94	93	91
3	107	103	99	96	106	101	98	95	99	96	94	97	94	92	94	93	91	94	93	90
4	104	98	94	91	102	97	94	91	95	92	90	94	91	89	92	90	88	92	90	87
5	101	95	90	87	99	94	90	87	92	89	86	91	88	86	89	87	85	89	87	84
6	98	91	87	84	96	90	86	84	89	86	83	88	85	83	87	84	82	87	84	81
7	95	88	84	81	94	87	83	80	86	83	80	85	82	80	84	81	79	84	81	78
8	92	85	81	78	91	85	80	78	84	80	77	83	79	77	82	79	77	82	79	76
9	89	82	78	75	88	82	78	75	81	77	75	80	77	75	80	77	74	80	77	73
10	87	80	76	73	86	79	75	73	79	75	73	78	75	72	77	74	72	77	74	71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	359686
5°	356283
10°	335019
15°	276029
20°	152870
25°	44325
30°	10938
35°	3935
40°	1002
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 0 cd/sqm

TEST NUMBER: P1304931

CATALOG NUMBER: P3DUS05R40B2750DE010 E3CBUS1MW_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.0	25.8
10°-20°	318.3	54.4
20°-30°	104.7	17.9
30°-40°	10.5	1.8
40°-50°	0.5	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	574.0	98.1
0°-40°	584.5	99.9
0°-60°	585.0	100.0
0°-90°	585.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	585.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1640	
5°	1619	151
15°	1216	318
25°	183	105
35°	15	11
45°	0	0
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1304931

CATALOG NUMBER: P3DUS05R40B2750DE010 E3CBUS1MW_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1640.3
2.5°	1637.7
5°	1618.6
7.5°	1578.9
10°	1504.6
12.5°	1389.6
15°	1215.9
17.5°	976.5
20°	655.1
22.5°	353.5
25°	183.2
27.5°	87.3
30°	43.2
32.5°	24.2
35°	14.7
37.5°	7.8
40°	3.5
42.5°	0.9
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)