

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1304937

Luminaire Tested: P3DUS05R45B2750DE010 E3CBUS1MW_5000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1304937
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-96)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3DUS05R45B2750DE010 E3CBUS1MW_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R45 optic, 5000K CCT AND, 80CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 628.0 lumens
Efficiency: N/A
Efficacy: 106.4 lumens/watt
Spacing Criteria (0/90/45): 0.67 / 0.67 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1304937

CATALOG NUMBER: P3DUS05R45B2750DE010 E3CBUS1MW_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1304937

CATALOG NUMBER: P3DUS05R45B2750DE010 E3CBUS1MW_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	115	112	110	108	112	110	108	107	106	105	103		102	101	100		99	98	97		96
2	110	106	103	100	108	105	102	99	101	99	97		99	97	95		96	94	93		91
3	106	101	97	94	104	100	96	93	97	94	92		95	92	90		93	91	89		87
4	102	96	92	88	101	95	91	88	93	90	87		91	88	86		89	87	85		84
5	98	92	87	84	97	91	87	83	89	86	83		88	85	82		86	84	81		80
6	95	88	83	80	94	87	83	79	86	82	79		84	81	78		83	80	78		77
7	92	84	79	76	90	84	79	76	82	78	76		81	78	75		80	77	75		74
8	88	81	76	73	87	80	76	73	79	75	72		78	75	72		78	74	72		71
9	85	78	73	70	84	77	73	70	76	72	70		76	72	69		75	72	69		68
10	82	75	70	67	82	74	70	67	74	70	67		73	69	67		72	69	66		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	304625
5°	302949
10°	284876
15°	232850
20°	170698
25°	94626
30°	37829
35°	12341
40°	2891
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 0 cd/sqm

TEST NUMBER: P1304937

CATALOG NUMBER: P3DUS05R45B2750DE010 E3CBUS1MW_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.5	20.5
10°-20°	281.0	44.7
20°-30°	182.0	29.0
30°-40°	35.2	5.6
40°-50°	1.2	0.2
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	591.5	94.2
0°-40°	626.7	99.8
0°-60°	628.0	100.0
0°-90°	628.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	628.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1389	
5°	1376	128
15°	1026	281
25°	391	182
35°	46	35
45°	0	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1304937

CATALOG NUMBER: P3DUS05R45B2750DE010 E3CBUS1MW_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1389.2
2.5°	1388.3
5°	1376.3
7.5°	1346.8
10°	1279.4
12.5°	1165.0
15°	1025.7
17.5°	881.8
20°	731.5
22.5°	557.2
25°	391.1
27.5°	253.7
30°	149.4
32.5°	84.9
35°	46.1
37.5°	24.0
40°	10.1
42.5°	1.8
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)