

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1304942

Luminaire Tested: P3DUS05R50B2750DE010 E3CBUS1MW_5000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1304942
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-91)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3DUS05R50B2750DE010 E3CBUS1MW_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R50 optic, 5000K CCT AND, 80CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 617.0 lumens
Efficiency: N/A
Efficacy: 104.6 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 0.71 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1304942

CATALOG NUMBER: P3DUS05R50B2750DE010 E3CBUS1MW_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1304942

CATALOG NUMBER: P3DUS05R50B2750DE010 E3CBUS1MW_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			
2	110	105	102	99	108	104	101	98	101	98	96	98	96	94	95	93	92	90			
3	105	100	95	92	103	98	94	91	96	93	90	93	91	89	91	89	87	86			
4	101	95	90	86	99	93	89	86	91	88	85	89	86	84	88	85	83	82			
5	97	90	85	81	95	89	84	81	87	83	80	86	82	79	84	81	79	78			
6	93	85	80	77	92	85	80	76	83	79	76	82	78	75	81	78	75	74			
7	89	81	76	73	88	81	76	73	80	75	72	79	75	72	77	74	72	70			
8	86	78	73	69	85	77	72	69	76	72	69	75	71	69	74	71	68	67			
9	83	74	69	66	82	74	69	66	73	69	66	72	68	65	71	68	65	64			
10	79	71	66	63	79	71	66	63	70	66	63	69	65	63	69	65	62	61			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	248752
5°	242790
10°	229366
15°	201590
20°	151633
25°	112119
30°	68010
35°	22486
40°	3950
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 0 cd/sqm

TEST NUMBER: P1304942

CATALOG NUMBER: P3DUS05R50B2750DE010 E3CBUS1MW_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.0	16.7
10°-20°	241.5	39.1
20°-30°	207.1	33.6
30°-40°	63.9	10.3
40°-50°	1.6	0.3
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	551.5	89.4
0°-40°	615.4	99.7
0°-60°	617.0	100.0
0°-90°	617.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	617.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1134	
5°	1103	103
15°	888	241
25°	463	207
35°	84	64
45°	0	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1304942

CATALOG NUMBER: P3DUS05R50B2750DE010 E3CBUS1MW_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1134.4
2.5°	1126.1
5°	1103.0
7.5°	1070.7
10°	1030.1
12.5°	965.5
15°	888.0
17.5°	789.2
20°	649.8
22.5°	531.7
25°	463.4
27.5°	376.6
30°	268.6
32.5°	163.4
35°	84.0
37.5°	37.8
40°	13.8
42.5°	1.8
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)