

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1304959

Luminaire Tested: P3DUS05R70B2750DE010 E3CBUS1MW_3000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1304959
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-95)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3DUS05R70B2750DE010 E3CBUS1MW_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R70 optic, 3000K CCT AND, 90CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 491.0 lumens
Efficiency: N/A
Efficacy: 83.2 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.99
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1304959

CATALOG NUMBER: P3DUS05R70B2750DE010 E3CBUS1MW_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1304959

CATALOG NUMBER: P3DUS05R70B2750DE010 E3CBUS1MW_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	114	111	108	106	111	109	107	105	105	103	101		101	100	98		98	96	95		94
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93	91	89		87
3	103	96	91	88	101	95	90	87	92	89	85		90	87	84		88	85	83		81
4	98	90	85	80	96	89	84	80	87	82	79		85	81	78		83	80	77		76
5	93	84	79	74	91	83	78	74	82	77	73		80	76	73		78	75	72		71
6	88	79	73	69	86	78	73	69	77	72	68		75	71	68		74	70	67		66
7	83	74	68	64	82	74	68	64	72	67	64		71	67	63		70	66	63		61
8	79	70	64	60	78	69	64	60	68	63	59		67	62	59		66	62	59		57
9	75	66	60	56	74	65	60	56	64	59	56		63	59	55		63	58	55		54
10	72	62	56	52	71	62	56	52	61	56	52		60	55	52		59	55	52		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	119420
5°	113691
10°	108771
15°	103769
20°	95955
25°	86957
30°	75075
35°	67539
40°	26278
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 0 cd/sqm

TEST NUMBER: P1304959

CATALOG NUMBER: P3DUS05R70B2750DE010 E3CBUS1MW_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.4	9.9
10°-20°	127.7	26.0
20°-30°	163.4	33.3
30°-40°	141.0	28.7
40°-50°	10.5	2.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	339.5	69.1
0°-40°	480.5	97.9
0°-60°	491.0	100.0
0°-90°	491.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	491.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	545	
5°	516	48
15°	457	128
25°	359	163
35°	252	141
45°	0	10
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1304959

CATALOG NUMBER: P3DUS05R70B2750DE010 E3CBUS1MW_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	544.6
2.5°	536.1
5°	516.5
7.5°	499.5
10°	488.5
12.5°	474.9
15°	457.1
17.5°	435.8
20°	411.2
22.5°	384.0
25°	359.4
27.5°	327.9
30°	296.5
32.5°	283.7
35°	252.3
37.5°	183.5
40°	91.8
42.5°	11.9
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)