

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1291874

Luminaire Tested: P3A09R20W2N902750DE010 E3CB1MW_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1291874
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R20W2N902750DE010 E3CB1MW_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 2700K CCT AND, 90CRI ,
E3CB1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 667.0 lumens
Efficiency: N/A
Efficacy: 74.1 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1291874

CATALOG NUMBER: P3A09R20W2N902750DE010 E3CB1MW_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1291874

CATALOG NUMBER: P3A09R20W2N902750DE010 E3CB1MW_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20				20				20
RC	80				70				50				30				10				0				0				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	102	102	102	102	102	102	102	102	100
1	116	114	112	110	113	112	110	109	108	106	105	104	103	102	101	100	99	99	98	97	97	96	95	95	94	93	92	91	98
2	112	109	107	104	110	108	105	103	104	103	101	102	100	99	99	98	97	97	96	95	95	94	93	92	91	90	89	88	95
3	109	105	102	100	108	104	101	99	102	99	97	99	98	96	97	96	95	95	94	93	93	92	91	90	89	88	87	86	93
4	107	102	99	96	105	101	98	96	99	97	95	97	95	93	96	94	92	92	91	90	90	89	88	87	86	85	84	83	91
5	104	99	96	93	103	98	95	93	97	94	92	95	93	91	94	92	91	91	90	89	89	88	87	86	85	84	83	82	90
6	102	97	93	91	101	96	93	90	95	92	90	94	91	89	93	90	89	89	88	87	87	86	85	84	83	82	81	80	88
7	100	94	91	88	99	94	91	88	93	90	88	92	89	87	91	89	87	87	86	85	85	84	83	82	81	80	79	78	86
8	98	92	89	86	97	92	89	86	91	88	86	90	88	86	89	87	85	85	84	83	83	82	81	80	79	78	77	76	85
9	96	90	87	85	95	90	87	85	89	86	84	88	86	84	87	85	83	83	82	81	81	80	79	78	77	76	75	74	83
10	94	89	85	83	93	88	85	83	88	85	83	87	84	83	86	84	82	82	81	80	80	79	78	77	76	75	74	73	82

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1035926
5°	899139
10°	555568
15°	192964
20°	59248
25°	20953
30°	7748
35°	3105
40°	1660
45°	651
50°	375
55°	421
60°	482
65°	259
70°	321
75°	424
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 651 cd/sqm

TEST NUMBER: P1291874

CATALOG NUMBER: P3A09R20W2N902750DE010 E3CB1MW_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	339.0	50.8
10°-20°	269.0	40.3
20°-30°	46.6	7.0
30°-40°	8.5	1.3
40°-50°	2.0	0.3
50°-60°	1.0	0.1
60°-70°	0.6	0.1
70°-80°	0.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	654.6	98.1
0°-40°	663.0	99.4
0°-60°	666.0	99.8
0°-90°	667.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	667.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4724	
5°	4085	339
15°	850	269
25°	87	47
35°	12	8
45°	2	2
55°	1	1
65°	0	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1291874

CATALOG NUMBER: P3A09R20W2N902750DE010 E3CB1MW_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	4724.2
1°	4701.5
2°	4611.7
3°	4467.6
4°	4298.7
5°	4084.8
6°	3839.9
7°	3554.8
8°	3230.1
9°	2865.3
10°	2495.1
12.5°	1573.9
15°	850.0
17.5°	454.0
20°	253.9
22.5°	145.2
25°	86.6
27.5°	52.8
30°	30.6
32.5°	18.0
35°	11.6
37.5°	7.9
40°	5.8
42.5°	3.7
45°	2.1
47.5°	1.1
50°	1.1
52.5°	1.1
55°	1.1
57.5°	1.1
60°	1.1
62.5°	0.5
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.5
77.5°	0.5
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)