

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1305005

Luminaire Tested: P3DUS09R55B2750DE010 E3CBUS1MW\_3500K

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1305005  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-92)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3DUS09R55B2750DE010 E3CBUS1MW\_3500K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R55 optic, 3500K CCT AND, 80CRI , E3CBUS1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 847.0 lumens  
Efficiency: N/A  
Efficacy: 64.7 lumens/watt  
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.77  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 13.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1305005  
CATALOG NUMBER: P3DUS09R55B2750DE010 E3CBUS1MW\_3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P1305005  
 CATALOG NUMBER: P3DUS09R55B2750DE010 E3CBUS1MW\_3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	98	98	97	95	95	95	95
2	109	105	102	99	107	103	100	97	100	98	95	97	95	93	95	93	91	90	90	90	90
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	87	85	85	85	85
4	100	94	89	85	99	93	88	85	91	87	84	89	86	83	87	84	82	81	81	81	81
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76	76	76	76
6	92	84	79	76	91	84	79	75	82	78	75	81	77	74	80	76	74	73	73	73	73
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69	69	69	69
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65	65	65	65
9	81	73	68	64	80	72	67	64	72	67	64	71	67	64	70	66	64	62	62	62	62
10	78	70	64	61	77	69	64	61	68	64	61	68	64	61	67	63	61	59	59	59	59

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	281425
5°	268654
10°	268621
15°	260183
20°	235384
25°	182261
30°	91305
35°	27492
40°	5868
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 0 cd/sqm



TEST NUMBER: P1305005

CATALOG NUMBER: P3DUS09R55B2750DE010 E3CBUS1MW\_3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	116.6	13.8
10°-20°	317.9	37.5
20°-30°	327.3	38.6
30°-40°	82.5	9.7
40°-50°	2.8	0.3
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	761.7	89.9
0°-40°	844.2	99.7
0°-60°	847.0	100.0
0°-90°	847.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	847.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1283	
5°	1220	117
15°	1146	318
25°	753	327
35°	103	82
45°	0	3
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1305005  
CATALOG NUMBER: P3DUS09R55B2750DE010 E3CBUS1MW\_3500K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1283.4
2.5°	1257.7
5°	1220.5
7.5°	1212.8
10°	1206.4
12.5°	1183.3
15°	1146.1
17.5°	1088.3
20°	1008.7
22.5°	900.9
25°	753.3
27.5°	566.0
30°	360.6
32.5°	209.2
35°	102.7
37.5°	48.8
40°	20.5
42.5°	5.1
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)