

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1291880

Luminaire Tested: P3A09R20W2N902750DE010 E3CD1MB_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1291880
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R20W2N902750DE010 E3CD1MB_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 3000K CCT AND, 90CRI ,
E3CD1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 736.1 lumens
Efficiency: N/A
Efficacy: 81.8 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1291880

CATALOG NUMBER: P3A09R20W2N902750DE010 E3CD1MB_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1291880

CATALOG NUMBER: P3A09R20W2N902750DE010 E3CD1MB_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20				20				20
RC	80				70				50				30				10				0				0				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	98	98	98	95	95	95	93	93	93
1	116	114	112	110	113	112	110	109	108	106	105	104	103	102	101	100	99	98	97	96	95	94	93	92	91	90	89	88	87
2	112	109	106	104	110	108	105	103	104	103	101	102	100	99	99	98	97	96	95	94	93	92	91	90	89	88	87	86	85
3	109	105	102	100	108	104	101	99	102	99	97	99	98	96	97	96	95	94	93	92	91	90	89	88	87	86	85	84	83
4	107	102	99	96	105	101	98	96	99	97	94	97	95	93	96	94	92	91	90	89	88	87	86	85	84	83	82	81	80
5	104	99	96	93	103	98	95	93	97	94	92	95	93	91	94	92	91	90	89	88	87	86	85	84	83	82	81	80	79
6	102	97	93	91	101	96	93	90	95	92	90	94	91	89	93	90	89	88	87	86	85	84	83	82	81	80	79	78	77
7	100	94	91	88	99	94	91	88	93	90	88	92	89	87	91	89	87	86	85	84	83	82	81	80	79	78	77	76	75
8	98	92	89	86	97	92	89	86	91	88	86	90	88	86	89	87	85	84	83	82	81	80	79	78	77	76	75	74	73
9	96	90	87	85	95	90	87	85	89	86	84	89	86	84	88	86	84	83	82	81	80	79	78	77	76	75	74	73	72
10	94	89	85	83	93	88	85	83	88	85	83	87	84	83	86	84	82	81	80	79	78	77	76	75	74	73	72	71	70

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1143088
5°	992161
10°	613059
15°	212941
20°	65386
25°	23106
30°	8558
35°	3426
40°	1832
45°	713
50°	409
55°	459
60°	526
65°	311
70°	385
75°	508
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 713 cd/sqm

TEST NUMBER: P1291880

CATALOG NUMBER: P3A09R20W2N902750DE010 E3CD1MB_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	374.1	50.8
10°-20°	296.8	40.3
20°-30°	51.4	7.0
30°-40°	9.3	1.3
40°-50°	2.1	0.3
50°-60°	1.1	0.1
60°-70°	0.7	0.1
70°-80°	0.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	722.3	98.1
0°-40°	731.6	99.4
0°-60°	734.8	99.8
0°-90°	736.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	736.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5213	
5°	4507	374
15°	938	297
25°	96	51
35°	13	9
45°	2	2
55°	1	1
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1291880

CATALOG NUMBER: P3A09R20W2N902750DE010 E3CD1MB_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	5212.9
1°	5187.9
2°	5088.8
3°	4929.8
4°	4743.4
5°	4507.4
6°	4237.1
7°	3922.5
8°	3564.2
9°	3161.7
10°	2753.3
12.5°	1736.7
15°	938.0
17.5°	501.0
20°	280.2
22.5°	160.2
25°	95.5
27.5°	58.3
30°	33.8
32.5°	19.8
35°	12.8
37.5°	8.7
40°	6.4
42.5°	4.1
45°	2.3
47.5°	1.2
50°	1.2
52.5°	1.2
55°	1.2
57.5°	1.2
60°	1.2
62.5°	0.6
65°	0.6
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.6
77.5°	0.6
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)