

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1305041

Luminaire Tested: P3DUS13R30B2750DE010 E3CBUS1MW_4000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1305041
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-88)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3DUS13R30B2750DE010 E3CBUS1MW_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R30 optic, 4000K CCT AND, 80CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1069.0 lumens
Efficiency: N/A
Efficacy: 56.0 lumens/watt
Spacing Criteria (0/90/45): 0.5 / 0.5 / 0.45
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1305041

CATALOG NUMBER: P3DUS13R30B2750DE010 E3CBUS1MW_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1305041

CATALOG NUMBER: P3DUS13R30B2750DE010 E3CBUS1MW_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99
1	115	113	111	110	113	111	109	108	107	106	105	103	103	102	100	99	99	97	96	96
2	112	108	105	103	110	107	104	102	104	101	100	101	99	98	98	97	96	94	93	93
3	108	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92	91	91
4	105	100	97	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89	88	88
5	102	97	93	90	101	96	93	90	95	91	89	93	90	88	92	89	88	87	86	86
6	100	94	90	87	99	93	90	87	92	89	86	91	88	86	90	87	85	84	83	83
7	97	91	87	84	96	91	87	84	90	86	84	89	86	83	88	85	83	82	81	81
8	95	89	85	82	94	88	84	82	87	84	82	86	83	81	86	83	81	80	79	79
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78	77	77
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76	75	75

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	958892
5°	931695
10°	788540
15°	474940
20°	171048
25°	48075
30°	12685
35°	4926
40°	1918
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 0 cd/sqm

TEST NUMBER: P1305041

CATALOG NUMBER: P3DUS13R30B2750DE010 E3CBUS1MW_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	383.0	35.8
10°-20°	556.7	52.1
20°-30°	115.0	10.8
30°-40°	13.4	1.3
40°-50°	0.9	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1054.7	98.7
0°-40°	1068.1	99.9
0°-60°	1069.0	100.0
0°-90°	1069.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1069.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4373	
5°	4233	383
15°	2092	557
25°	199	115
35°	18	13
45°	0	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1305041

CATALOG NUMBER: P3DUS13R30B2750DE010 E3CBUS1MW_4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	4372.9
2.5°	4337.8
5°	4232.7
7.5°	4000.6
10°	3541.4
12.5°	2881.9
15°	2092.1
17.5°	1339.1
20°	733.0
22.5°	367.3
25°	198.7
27.5°	108.5
30°	50.1
32.5°	30.1
35°	18.4
37.5°	11.7
40°	6.7
42.5°	1.7
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)