

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1305061

Luminaire Tested: P3DUS13R50B2750DE010 E3CBUS1MW_4000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1305061
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-91)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3DUS13R50B2750DE010 E3CBUS1MW_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R50 optic, 4000K CCT AND, 80CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1116.0 lumens
Efficiency: N/A
Efficacy: 58.4 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 0.71 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1305061

CATALOG NUMBER: P3DUS13R50B2750DE010 E3CBUS1MW_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1305061

CATALOG NUMBER: P3DUS13R50B2750DE010 E3CBUS1MW_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	94	93
2	110	105	102	99	108	104	101	98	101	98	96	98	96	94	95	93	92	90	89	88
3	105	100	95	92	103	98	94	91	96	93	90	93	91	89	91	89	87	86	85	84
4	101	95	90	86	99	93	89	86	91	88	85	89	86	84	88	85	83	82	81	80
5	97	90	85	81	95	89	84	81	87	83	80	86	82	79	84	81	79	78	77	76
6	93	85	80	77	92	85	80	76	83	79	76	82	78	75	81	78	75	74	73	72
7	89	81	76	73	88	81	76	73	80	75	72	79	75	72	77	74	72	70	69	68
8	86	78	73	69	85	77	72	69	76	72	69	75	71	69	74	71	68	67	66	65
9	83	74	69	66	82	74	69	66	73	69	66	72	68	65	71	68	65	64	63	62
10	79	71	66	63	79	71	66	63	70	66	63	69	65	63	69	65	62	61	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	449942
5°	439158
10°	414867
15°	364610
20°	274284
25°	202778
30°	123006
35°	40662
40°	7156
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 0 cd/sqm

TEST NUMBER: P1305061

CATALOG NUMBER: P3DUS13R50B2750DE010 E3CBUS1MW_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.3	16.7
10°-20°	436.8	39.1
20°-30°	374.6	33.6
30°-40°	115.5	10.4
40°-50°	2.9	0.3
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	997.6	89.4
0°-40°	1113.1	99.7
0°-60°	1116.0	100.0
0°-90°	1116.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1116.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2052	
5°	1995	186
15°	1606	437
25°	838	375
35°	152	116
45°	0	3
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1305061

CATALOG NUMBER: P3DUS13R50B2750DE010 E3CBUS1MW_4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	2051.9
2.5°	2036.8
5°	1995.1
7.5°	1936.7
10°	1863.2
12.5°	1746.3
15°	1606.1
17.5°	1427.5
20°	1175.4
22.5°	961.7
25°	838.1
27.5°	681.2
30°	485.8
32.5°	295.5
35°	151.9
37.5°	68.5
40°	25.0
42.5°	3.3
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)