

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293521

Luminaire Tested: P3A09R45W2N902750DE010 E3DL1H_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1293521
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R45W2N902750DE010 E3DL1H_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R45 optic, 2700K CCT AND, 90CRI , E3DL1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 591.0 lumens
Efficiency: N/A
Efficacy: 65.7 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1293521

CATALOG NUMBER: P3A09R45W2N902750DE010 E3DL1H_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1293521

CATALOG NUMBER: P3A09R45W2N902750DE010 E3DL1H_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	109	107		111	109	107	105		105	103	102		101	100	99		98	97	96
2	109	104	100	97		106	102	99	96		99	96	94		96	94	92		93	91	90
3	104	98	93	89		102	96	92	88		94	90	87		91	88	86		89	87	84
4	99	92	87	83		97	91	86	82		89	85	81		87	83	80		85	82	79
5	94	87	81	77		93	86	81	77		84	80	76		82	79	76		81	78	75
6	90	82	77	73		89	81	76	72		80	75	72		78	74	71		77	74	71
7	86	78	72	68		85	77	72	68		76	71	68		75	71	67		74	70	67
8	83	74	68	65		82	73	68	65		72	68	64		71	67	64		70	67	64
9	79	70	65	61		78	70	65	61		69	64	61		68	64	61		67	63	61
10	76	67	62	58		75	67	62	58		66	61	58		65	61	58		65	61	58

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	221934
5°	216728
10°	199239
15°	168809
20°	130981
25°	91554
30°	57680
35°	33943
40°	19207
45°	9334
50°	3241
55°	2638
60°	2544
65°	2491
70°	2372
75°	2203
80°	2020
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 9334 cd/sqm

TEST NUMBER: P1293521

CATALOG NUMBER: P3A09R45W2N902750DE010 E3DL1H_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.1	15.4
10°-20°	204.2	34.6
20°-30°	173.4	29.3
30°-40°	82.7	14.0
40°-50°	24.9	4.2
50°-60°	6.3	1.1
60°-70°	4.7	0.8
70°-80°	2.8	0.5
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	468.8	79.3
0°-40°	551.5	93.3
0°-60°	582.7	98.6
0°-90°	591.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	591.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1012	
5°	985	91
15°	744	204
25°	378	173
35°	127	83
45°	30	25
55°	7	6
65°	5	5
75°	3	3
85°	0	1
90°	0	

TEST NUMBER: P1293521

CATALOG NUMBER: P3A09R45W2N902750DE010 E3DL1H_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1012.1
2.5°	1005.8
5°	984.6
7.5°	948.2
10°	894.8
12.5°	824.0
15°	743.6
17.5°	654.3
20°	561.3
22.5°	466.7
25°	378.4
27.5°	298.1
30°	227.8
32.5°	171.2
35°	126.8
37.5°	93.5
40°	67.1
42.5°	46.5
45°	30.1
47.5°	16.9
50°	9.5
52.5°	7.4
55°	6.9
57.5°	6.3
60°	5.8
62.5°	5.3
65°	4.8
67.5°	4.2
70°	3.7
72.5°	3.2
75°	2.6
77.5°	2.1
80°	1.6
82.5°	1.1
85°	0.5
87.5°	0.5
90°	0.0

(END OF REPORT)