

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293552

Luminaire Tested: P3A09R45W2N902750DE010 E3DLD1H_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1293552
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R45W2N902750DE010 E3DLD1H_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R45 optic, 3000K CCT AND, 90CRI ,
E3DLD1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 506.0 lumens
Efficiency: N/A
Efficacy: 56.2 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1293552
CATALOG NUMBER: P3A09R45W2N902750DE010 E3DLD1H_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1293552
 CATALOG NUMBER: P3A09R45W2N902750DE010 E3DLD1H_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91	91	91	91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83	83	83	83
3	99	92	86	82	97	90	85	81	88	83	80	85	81	78	83	80	77	75	75	75	75
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69	69	69	69
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63	63	63	63
6	83	73	66	61	81	72	66	61	71	65	61	69	64	60	68	63	60	58	58	58	58
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	64	59	55	54	54	54	54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	52	50	50	50	50
9	70	60	53	49	69	59	53	49	58	52	48	57	52	48	56	52	48	47	47	47	47
10	67	56	50	45	66	56	49	45	55	49	45	54	49	45	53	48	45	44	44	44	44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	107294
5°	105393
10°	99709
15°	90943
20°	80414
25°	69851
30°	59959
35°	49951
40°	37213
45°	22793
50°	10541
55°	8258
60°	7938
65°	7264
70°	6732
75°	6439
80°	5935
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 22793 cd/sqm



TEST NUMBER: P1293552

CATALOG NUMBER: P3A09R45W2N902750DE010 E3DLD1H_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.7	8.8
10°-20°	111.5	22.0
20°-30°	132.5	26.2
30°-40°	115.1	22.8
40°-50°	57.8	11.4
50°-60°	20.0	4.0
60°-70°	14.0	2.8
70°-80°	7.8	1.5
80°-90°	2.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	288.8	57.1
0°-40°	403.9	79.8
0°-60°	481.7	95.2
0°-90°	506.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	506.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	489	
5°	479	45
15°	401	112
25°	289	133
35°	187	115
45°	74	58
55°	22	20
65°	14	14
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P1293552
CATALOG NUMBER: P3A09R45W2N902750DE010 E3DLD1H_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	489.3
2.5°	486.9
5°	478.8
7.5°	465.9
10°	447.8
12.5°	425.7
15°	400.6
17.5°	372.6
20°	344.6
22.5°	316.1
25°	288.7
27.5°	262.4
30°	236.8
32.5°	212.3
35°	186.6
37.5°	159.2
40°	130.0
42.5°	101.5
45°	73.5
47.5°	48.4
50°	30.9
52.5°	23.9
55°	21.6
57.5°	19.8
60°	18.1
62.5°	16.3
65°	14.0
67.5°	12.2
70°	10.5
72.5°	8.7
75°	7.6
77.5°	5.8
80°	4.7
82.5°	3.5
85°	1.7
87.5°	1.2
90°	0.0

(END OF REPORT)