

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293685

Luminaire Tested: P3A09R45W2N902765DE010 E3DLD1GPH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1293685
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R45W2N902765DE010 E3DLD1GPH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R45 optic, 3000K CCT AND, 90CRI ,
E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 248.0 lumens
Efficiency: N/A
Efficacy: 27.6 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1293685

CATALOG NUMBER: P3A09R45W2N902765DE010 E3DLD1GPH_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1293685

CATALOG NUMBER: P3A09R45W2N902765DE010 E3DLD1GPH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83		
3	99	92	86	82	97	90	85	81	88	83	80	85	81	78	83	80	77	75		
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69		
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63		
6	83	73	66	61	81	72	66	61	71	65	61	69	64	60	68	63	60	58		
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	64	59	55	54		
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	52	50		
9	70	60	53	49	69	59	53	49	58	52	48	57	52	48	56	52	48	47		
10	67	56	50	45	66	56	49	45	55	49	45	54	49	45	53	48	45	44		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	52584
5°	51640
10°	48875
15°	44563
20°	39413
25°	34236
30°	29372
35°	24494
40°	18234
45°	11164
50°	5151
55°	4052
60°	3903
65°	3580
70°	3270
75°	3135
80°	2904
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11164 cd/sqm

TEST NUMBER: P1293685

CATALOG NUMBER: P3A09R45W2N902765DE010 E3DLD1GPH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	21.9	8.8
10°-20°	54.7	22.0
20°-30°	64.9	26.2
30°-40°	56.4	22.8
40°-50°	28.3	11.4
50°-60°	9.8	4.0
60°-70°	6.9	2.8
70°-80°	3.9	1.6
80°-90°	1.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	141.5	57.1
0°-40°	198.0	79.8
0°-60°	236.1	95.2
0°-90°	248.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	248.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	240	
5°	235	22
15°	196	55
25°	142	65
35°	92	56
45°	36	28
55°	11	10
65°	7	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1293685

CATALOG NUMBER: P3A09R45W2N902765DE010 E3DLD1GPH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	239.8
2.5°	238.6
5°	234.6
7.5°	228.4
10°	219.5
12.5°	208.6
15°	196.3
17.5°	182.6
20°	168.9
22.5°	154.9
25°	141.5
27.5°	128.6
30°	116.0
32.5°	104.0
35°	91.5
37.5°	78.0
40°	63.7
42.5°	49.7
45°	36.0
47.5°	23.7
50°	15.1
52.5°	11.7
55°	10.6
57.5°	9.7
60°	8.9
62.5°	8.0
65°	6.9
67.5°	6.0
70°	5.1
72.5°	4.3
75°	3.7
77.5°	2.9
80°	2.3
82.5°	1.7
85°	0.9
87.5°	0.6
90°	0.0

(END OF REPORT)