

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1294017

Luminaire Tested: P3A09R50W2N902765DE010 E3DLD1LI_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1294017
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R50W2N902765DE010 E3DLD1LI_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 3500K CCT AND, 90CRI ,
E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 517.9 lumens
Efficiency: N/A
Efficacy: 57.5 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1294017

CATALOG NUMBER: P3A09R50W2N902765DE010 E3DLD1LI_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1294017

CATALOG NUMBER: P3A09R50W2N902765DE010 E3DLD1LI_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	102	103	101	99		99	97	96		95	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89	86	84	83
3	99	92	86	81	97	90	85	81	88	83	79		85	81	78		83	80	77	75
4	93	85	78	73	91	83	77	73	81	76	72		79	75	71		77	73	70	69
5	88	78	72	67	86	77	71	66	75	70	66		74	69	65		72	68	64	63
6	83	73	66	61	81	72	65	61	70	65	60		69	64	60		67	63	59	58
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63	59	55	53
8	74	63	57	52	73	63	56	52	61	56	52		60	55	51		59	55	51	50
9	70	59	53	48	69	59	52	48	58	52	48		57	52	48		56	51	48	46
10	66	56	49	45	65	55	49	45	54	49	45		54	48	45		53	48	45	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	105277
5°	103720
10°	99130
15°	91805
20°	82491
25°	72512
30°	61680
35°	50005
40°	37556
45°	24189
50°	11496
55°	9022
60°	8552
65°	7990
70°	7181
75°	6524
80°	5935
85°	6038

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 24189 cd/sqm

TEST NUMBER: P1294017

CATALOG NUMBER: P3A09R50W2N902765DE010 E3DLD1LI_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.2	8.5
10°-20°	112.7	21.8
20°-30°	137.0	26.4
30°-40°	116.2	22.4
40°-50°	60.3	11.6
50°-60°	21.8	4.2
60°-70°	15.0	2.9
70°-80°	8.2	1.6
80°-90°	2.6	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	293.9	56.7
0°-40°	410.0	79.2
0°-60°	492.1	95.0
0°-90°	517.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	517.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	480	
5°	471	44
15°	404	113
25°	300	137
35°	187	116
45°	78	60
55°	24	22
65°	15	15
75°	8	8
85°	2	3
90°	0	



TEST NUMBER: P1294017

CATALOG NUMBER: P3A09R50W2N902765DE010 E3DLD1LI_3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	480.1
2.5°	478.3
5°	471.2
7.5°	460.5
10°	445.2
12.5°	425.7
15°	404.4
17.5°	380.1
20°	353.5
22.5°	326.3
25°	299.7
27.5°	272.0
30°	243.6
32.5°	215.2
35°	186.8
37.5°	159.0
40°	131.2
42.5°	104.6
45°	78.0
47.5°	52.0
50°	33.7
52.5°	26.0
55°	23.6
57.5°	21.3
60°	19.5
62.5°	17.1
65°	15.4
67.5°	13.0
70°	11.2
72.5°	9.5
75°	7.7
77.5°	5.9
80°	4.7
82.5°	3.5
85°	2.4
87.5°	1.2
90°	0.0

(END OF REPORT)