

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1294123

Luminaire Tested: P3A09R55W2N902750DE010 E3D1WH_4000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1294123
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R55W2N902750DE010 E3D1WH_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 4000K CCT AND, 90CRI ,
E3D1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 764.0 lumens
Efficiency: N/A
Efficacy: 84.9 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1294123
CATALOG NUMBER: P3A09R55W2N902750DE010 E3D1WH_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1294123
 CATALOG NUMBER: P3A09R55W2N902750DE010 E3D1WH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95		
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89		
3	104	98	94	90	102	97	93	90	95	91	88	92	89	87	90	88	86	84		
4	100	93	88	84	98	92	87	84	90	86	83	88	84	82	86	83	81	79		
5	95	88	82	79	94	87	82	78	85	81	78	84	80	77	82	79	76	75		
6	91	83	78	74	90	82	77	74	81	76	73	80	76	73	78	75	72	71		
7	87	79	73	70	86	78	73	69	77	72	69	76	72	69	75	71	68	67		
8	83	75	69	66	82	74	69	65	73	69	65	72	68	65	71	68	65	63		
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	64	61	60		
10	77	68	62	59	76	67	62	59	67	62	59	66	62	59	65	61	58	57		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	221561
5°	213713
10°	221350
15°	218231
20°	201968
25°	163340
30°	97888
35°	33167
40°	9131
45°	4062
50°	1194
55°	229
60°	132
65°	156
70°	192
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4062 cd/sqm



TEST NUMBER: P1294123

CATALOG NUMBER: P3A09R55W2N902750DE010 E3D1WH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.9	12.3
10°-20°	267.6	35.0
20°-30°	297.5	38.9
30°-40°	92.6	12.1
40°-50°	11.1	1.5
50°-60°	0.9	0.1
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	659.1	86.3
0°-40°	751.7	98.4
0°-60°	763.7	100.0
0°-90°	764.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	764.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1010	
5°	971	94
15°	961	268
25°	675	298
35°	124	93
45°	13	11
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1294123
CATALOG NUMBER: P3A09R55W2N902750DE010 E3D1WH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1010.4
1°	1006.6
2°	996.7
3°	984.5
4°	973.5
5°	970.9
6°	973.8
7°	979.9
8°	986.8
9°	992.4
10°	994.1
11°	992.9
12°	988.3
13°	981.0
14°	972.6
15°	961.3
16°	948.2
17°	931.7
18°	913.1
19°	890.8
20°	865.5
21°	836.8
22°	802.8
23°	765.4
24°	722.4
25°	675.1
26°	623.2
27°	568.0
28°	509.1
29°	448.4
30°	386.6
31°	324.5
32°	263.8
32.5°	236.8
33°	209.0
34°	161.7
35°	123.9
36°	94.3
37°	69.9
37.5°	59.8
38°	52.0
39°	39.5
40°	31.9
42.5°	20.3
45°	13.1



TEST NUMBER: P1294123
CATALOG NUMBER: P3A09R55W2N902750DE010 E3D1WH_4000K

CANDELA DISTRIBUTION (continued):

	0°
47.5°	7.8
50°	3.5
52.5°	1.2
55°	0.6
57.5°	0.3
60°	0.3
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)