

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1306122

Luminaire Tested: P3SQAS17R509024DE010 E3SQCA301MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1306122
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-53)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3SQAS17R509024DE010 E3SQCA301MMS
Description: 3in Adjustable LED luminaire with, R50 optic, 2400K CCT AND, 90CRI , E3SQCA301MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1158.0 lumens
Efficiency: N/A
Efficacy: 54.6 lumens/watt
Spacing Criteria (0/90/45): 1.8 / 0.48 / 1.24
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1306122

CATALOG NUMBER: P3SQAS17R509024DE010 E3SQCA301MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1306122

CATALOG NUMBER: P3SQAS17R509024DE010 E3SQCA301MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96	94	93	91
2	105	100	95	91	103	98	93	90	94	91	88		91	88	86		89	86	84	82
3	98	91	85	80	96	89	84	79	86	82	78		84	80	77		82	78	75	74
4	92	83	76	71	90	81	75	70	79	74	70		77	72	69		75	71	68	66
5	86	76	68	63	84	75	68	63	73	67	62		71	66	62		69	65	61	59
6	80	69	62	57	78	68	62	57	67	61	56		65	60	56		64	59	55	54
7	75	64	56	51	73	63	56	51	61	55	51		60	55	50		59	54	50	48
8	70	59	51	46	69	58	51	46	57	50	46		56	50	46		55	49	46	44
9	66	54	47	42	64	54	47	42	53	46	42		52	46	42		51	45	42	40
10	62	50	43	39	61	50	43	39	49	43	38		48	42	38		47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	123828	123828	123828	123828	123828
5°	204016	193609	118994	35337	17668
10°	198838	203210	95344	1784	2378
15°	202725	203937	57109	1819	606
20°	319541	208787	23514	0	0
25°	416576	243253	5606	0	0
30°	467573	240568	219		

TEST NUMBER: P1306122

CATALOG NUMBER: P3SQAS17R509024DE010 E3SQCA301MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.4	5.2
10°-20°	152.1	13.1
20°-30°	292.2	25.2
30°-40°	340.1	29.4
40°-50°	243.4	21.0
50°-60°	67.7	5.9
60°-70°	0.4	0.0
70°-80°	0.7	0.1
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	504.7	43.6
0°-40°	844.8	73.0
0°-60°	1156.0	99.8
0°-90°	1158.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1158.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	719	719	719	719	719	
5°	1180	1120	688	204	102	108
15°	1137	1144	320	10	3	367
25°	2192	1280	30	0	0	997
35°	2327	1127	0	0	0	1440
45°	1101	558	0	0	0	1035
55°	272	0	0	0	0	342
65°	0	1	1	0	0	0
75°	0	1	1	0	0	0
85°	0	1	2	1	0	0
90°	0	0	0	0	0	

TEST NUMBER: P1306122

CATALOG NUMBER: P3SQAS17R509024DE010 E3SQCA301MMS

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	45°	67.5°	90°
0°	719.0	719.0	719.0	719.0	719.0	719.0	719.0	719.0	719.0	719.0	719.0
2.5°	1045.0	1050.6	1051.8	1038.2	1040.4	1021.1	1022.2	1008.6	975.7	861.0	722.4
5°	1180.1	1176.7	1180.1	1175.6	1180.1	1168.8	1162.0	1156.3	1119.9	957.5	688.3
7.5°	1167.6	1163.1	1169.9	1172.2	1180.1	1176.7	1177.9	1181.3	1168.8	1009.8	630.4
10°	1137.0	1135.8	1139.2	1139.2	1148.3	1149.5	1154.0	1160.8	1162.0	1027.9	545.2
12.5°	1107.4	1104.0	1104.0	1102.9	1107.4	1106.3	1117.7	1133.6	1155.1	1016.6	428.2
15°	1137.0	1133.6	1129.0	1116.5	1107.4	1097.2	1098.3	1108.6	1143.8	987.0	320.3
17.5°	1375.5	1357.3	1334.6	1294.8	1252.8	1180.1	1137.0	1109.7	1130.2	941.6	213.5
20°	1743.5	1735.6	1699.2	1634.5	1566.3	1459.5	1326.7	1219.9	1139.2	884.8	128.3
21°	1883.2	1878.7	1840.0	1779.8	1702.6	1573.1	1436.8	1308.5	1157.4	861.0	101.1
22°	2026.3	2009.3	1978.6	1911.6	1831.0	1701.5	1549.3	1407.3	1193.8	830.3	77.2
23°	2118.3	2108.1	2075.2	2021.8	1944.5	1818.5	1662.9	1508.4	1229.0	796.2	57.9
24°	2166.0	2162.6	2136.5	2099.0	2033.1	1904.8	1757.1	1598.1	1258.5	756.5	42.0
25°	2192.2	2180.8	2164.9	2137.6	2087.7	1976.3	1844.6	1676.5	1280.1	716.7	29.5
26°	2208.1	2201.2	2176.3	2152.4	2104.7	2013.8	1901.4	1724.2	1285.8	667.9	20.4
27°	2226.2	2210.3	2186.5	2158.1	2104.7	2025.2	1923.0	1744.6	1278.9	617.9	13.6
28°	2245.5	2234.2	2201.2	2164.9	2101.3	2025.2	1915.0	1717.4	1258.5	570.2	8.0
29°	2283.0	2268.3	2227.4	2174.0	2102.4	2022.9	1884.3	1660.6	1231.2	516.8	4.5
30°	2351.2	2320.5	2270.5	2195.6	2110.4	2018.4	1833.2	1575.4	1209.7	456.6	1.1



TEST NUMBER: P1306122

CATALOG NUMBER: P3SQAS17R509024DE010 E3SQCA301MMS

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	45°	67.5°	90°
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	1.1	1.1	1.1	2.3
85°	0.0	0.0	0.0	0.0	0.0	0.0	1.1	1.1	1.1	1.1	2.3
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	1.1	1.1	1.1	2.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1306122

CATALOG NUMBER: P3SQAS17R509024DE010 E3SQCA301MMS

CANDELA DISTRIBUTION (continued):

	112.5°	135°	157.5°	180°
0°	719.0	719.0	719.0	719.0
2.5°	575.9	441.8	357.8	363.5
5°	404.4	204.4	126.1	102.2
7.5°	241.9	62.5	12.5	10.2
10°	113.6	10.2	11.4	13.6
12.5°	34.1	9.1	12.5	11.4
15°	9.1	10.2	5.7	3.4
17.5°	3.4	4.5	0.0	0.0
20°	2.3	0.0	0.0	0.0
21°	2.3	0.0	0.0	0.0
22°	1.1	0.0	0.0	0.0
23°	0.0	0.0	0.0	0.0
24°	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0
26°	0.0	0.0	0.0	0.0
27°	0.0	0.0	0.0	0.0
28°	0.0	0.0	0.0	0.0
29°	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0
31°	0.0	0.0	0.0	0.0
32°	0.0	0.0	0.0	0.0
33°	0.0	0.0	0.0	0.0
34°	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0
36°	0.0	0.0	0.0	0.0
37°	0.0	0.0	0.0	0.0
38°	0.0	0.0	0.0	0.0
39°	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0
65°	1.1	0.0	0.0	0.0
67.5°	1.1	0.0	0.0	0.0
70°	1.1	0.0	0.0	0.0
72.5°	1.1	0.0	0.0	0.0
75°	1.1	0.0	0.0	0.0
77.5°	1.1	0.0	0.0	0.0
80°	1.1	1.1	0.0	0.0



TEST NUMBER: P1306122

CATALOG NUMBER: P3SQAS17R509024DE010 E3SQCA301MMS

CANDELA DISTRIBUTION (continued):

	112.5°	135°	157.5°	180°
82.5°	1.1	1.1	0.0	0.0
85°	1.1	1.1	0.0	0.0
87.5°	1.1	1.1	0.0	0.0
90°	0.0	0.0	0.0	0.0

(END OF REPORT)