

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302904

Luminaire Tested: P3DUS02R089024DE010 E3CBUS1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1302904
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2408-211-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3DUS02R089024DE010 E3CBUS1MMS
Description: 3in Adjustable LED luminaire with, R08 optic, 2400K CCT AND, 90CRI , E3CBUS1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 218.1 lumens
Efficiency: N/A
Efficacy: 44.5 lumens/watt
Spacing Criteria (0/90/45): 0.16 / 0.16 / 0.16
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 4.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1302904

CATALOG NUMBER: P3DUS02R089024DE010 E3CBUS1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1302904

CATALOG NUMBER: P3DUS02R089024DE010 E3CBUS1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	116	114	113	111		114	112	111	110		108	107	106		105	104	103		101	101	100
2	113	111	108	106		111	109	107	105		106	104	103		103	102	101		101	100	99
3	111	107	105	103		109	106	104	102		104	102	100		102	100	99		100	98	97
4	109	105	102	100		108	104	101	99		102	100	98		100	99	97		99	97	96
5	107	103	100	98		106	102	99	97		101	98	96		99	97	96		98	96	95
6	105	101	98	96		104	100	98	96		99	97	95		98	96	95		97	95	94
7	104	99	97	95		103	99	96	94		98	96	94		97	95	94		96	94	93
8	103	98	95	93		102	98	95	93		97	95	93		96	94	93		95	94	92
9	101	97	94	92		101	97	94	92		96	94	92		95	93	92		95	93	91
10	100	96	93	91		100	96	93	91		95	93	91		94	92	91		94	92	90

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1236414
5°	515583
10°	82964
15°	23791
20°	8004
25°	3532
30°	1950
35°	1392
40°	1231
45°	806
50°	580
55°	344
60°	395
65°	467
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 806 cd/sqm

TEST NUMBER: P1302904

CATALOG NUMBER: P3DUS02R089024DE010 E3CBUS1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	168.2	77.1
10°-20°	35.2	16.1
20°-30°	7.7	3.5
30°-40°	3.3	1.5
40°-50°	2.0	0.9
50°-60°	0.9	0.4
60°-70°	0.8	0.4
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	211.0	96.8
0°-40°	214.3	98.3
0°-60°	217.3	99.6
0°-90°	218.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	218.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5638	
5°	2342	168
15°	105	35
25°	15	8
35°	5	3
45°	3	2
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1302904

CATALOG NUMBER: P3DUS02R089024DE010 E3CBUS1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	5638.5
2.5°	4713.0
5°	2342.3
7.5°	873.2
10°	372.6
12.5°	192.3
15°	104.8
17.5°	59.2
20°	34.3
22.5°	22.3
25°	14.6
27.5°	11.2
30°	7.7
32.5°	6.0
35°	5.2
37.5°	4.3
40°	4.3
42.5°	3.4
45°	2.6
47.5°	1.7
50°	1.7
52.5°	0.9
55°	0.9
57.5°	0.9
60°	0.9
62.5°	0.9
65°	0.9
67.5°	0.9
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)