

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1303246

Luminaire Tested: P3DUS24R709027D010 E3CBUS1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1303246
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-95)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3DUS24R709027D010 E3CBUS1MW
Description: 3in Adjustable LED luminaire with, R70 optic, 2700K CCT AND, 90CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2269.0 lumens
Efficiency: N/A
Efficacy: 78.8 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.99
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1303246

CATALOG NUMBER: P3DUS24R709027D010 E3CBUS1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1303246

CATALOG NUMBER: P3DUS24R709027D010 E3CBUS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	107	105	105	103	101		101	100	98		98
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93
3	103	96	91	88	101	95	90	87	92	89	85		90	87	84		88
4	98	90	85	80	96	89	84	80	87	82	79		85	81	78		83
5	93	84	79	74	91	83	78	74	82	77	73		80	76	73		78
6	88	79	73	69	86	78	73	69	77	72	68		75	71	68		74
7	83	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	62	59		66
9	75	66	60	56	74	65	60	56	64	59	56		63	59	55		63
10	72	62	56	52	71	62	56	52	61	56	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	551820
5°	525422
10°	502640
15°	479481
20°	443395
25°	401805
30°	346914
35°	312129
40°	121370
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 0 cd/sqm

TEST NUMBER: P1303246

CATALOG NUMBER: P3DUS24R709027D010 E3CBUS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	223.8	9.9
10°-20°	590.1	26.0
20°-30°	755.0	33.3
30°-40°	651.7	28.7
40°-50°	48.5	2.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1568.8	69.1
0°-40°	2220.5	97.9
0°-60°	2269.0	100.0
0°-90°	2269.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2269.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2516	
5°	2387	224
15°	2112	590
25°	1661	755
35°	1166	652
45°	0	49
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1303246

CATALOG NUMBER: P3DUS24R709027D010 E3CBUS1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	2516.5
2.5°	2477.2
5°	2387.0
7.5°	2308.4
10°	2257.4
12.5°	2194.6
15°	2112.1
17.5°	2014.0
20°	1900.1
22.5°	1774.5
25°	1660.7
27.5°	1515.4
30°	1370.1
32.5°	1311.3
35°	1166.0
37.5°	848.0
40°	424.0
42.5°	55.0
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)