

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1303396

Luminaire Tested: P3DUS17R509030DE010 E3CBUS1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1303396
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-91)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3DUS17R509030DE010 E3CBUS1MW
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 90CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1868.0 lumens
Efficiency: N/A
Efficacy: 88.1 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 0.71 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1303396

CATALOG NUMBER: P3DUS17R509030DE010 E3CBUS1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1303396

CATALOG NUMBER: P3DUS17R509030DE010 E3CBUS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	110	105	102	99		108	104	101	98		101	98	96		98	96	94		95	93	92
3	105	100	95	92		103	98	94	91		96	93	90		93	91	89		91	89	87
4	101	95	90	86		99	93	89	86		91	88	85		89	86	84		88	85	83
5	97	90	85	81		95	89	84	81		87	83	80		86	82	79		84	81	79
6	93	85	80	77		92	85	80	76		83	79	76		82	78	75		81	78	75
7	89	81	76	73		88	81	76	73		80	75	72		79	75	72		77	74	72
8	86	78	73	69		85	77	72	69		76	72	69		75	71	69		74	71	68
9	83	74	69	66		82	74	69	66		73	69	66		72	68	65		71	68	65
10	79	71	66	63		79	71	66	63		70	66	63		69	65	63		69	65	62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	753119
5°	735085
10°	694420
15°	610310
20°	459100
25°	339431
30°	205905
35°	68074
40°	11994
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 0 cd/sqm

TEST NUMBER: P1303396

CATALOG NUMBER: P3DUS17R509030DE010 E3CBUS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	311.8	16.7
10°-20°	731.1	39.1
20°-30°	627.0	33.6
30°-40°	193.3	10.4
40°-50°	4.8	0.3
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1669.8	89.4
0°-40°	1863.2	99.7
0°-60°	1868.0	100.0
0°-90°	1868.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1868.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3434	
5°	3340	312
15°	2688	731
25°	1403	627
35°	254	193
45°	0	5
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1303396

CATALOG NUMBER: P3DUS17R509030DE010 E3CBUS1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	3434.5
2.5°	3409.4
5°	3339.5
7.5°	3241.7
10°	3118.7
12.5°	2923.1
15°	2688.4
17.5°	2389.3
20°	1967.4
22.5°	1609.7
25°	1402.9
27.5°	1140.2
30°	813.2
32.5°	494.6
35°	254.3
37.5°	114.6
40°	41.9
42.5°	5.6
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)