

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1303747

Luminaire Tested: P3DUS17R409040DE010 E3CBUS1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1303747
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-90)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3DUS17R409040DE010 E3CBUS1MW
Description: 3in Adjustable LED luminaire with, R40 optic, 4000K CCT AND, 90CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2035.0 lumens
Efficiency: N/A
Efficacy: 96.0 lumens/watt
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.55
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1303747

CATALOG NUMBER: P3DUS17R409040DE010 E3CBUS1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1303747

CATALOG NUMBER: P3DUS17R409040DE010 E3CBUS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	113	111	109	107	107	105	104		103	102	101		100
2	111	107	104	102	109	106	103	101	103	100	98		100	98	96		97
3	107	103	99	96	106	101	98	95	99	96	94		97	94	92		94
4	104	98	94	91	102	97	94	91	95	92	90		94	91	89		92
5	101	95	90	87	99	94	90	87	92	89	86		91	88	86		89
6	98	91	87	84	96	90	86	84	89	86	83		88	85	83		87
7	95	88	84	81	94	87	83	80	86	83	80		85	82	80		84
8	92	85	81	78	91	85	80	78	84	80	77		83	79	77		82
9	89	82	78	75	88	82	78	75	81	77	75		80	77	75		80
10	87	80	76	73	86	79	75	73	79	75	73		78	75	72		77

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1251172
5°	1239420
10°	1165398
15°	960233
20°	531743
25°	154194
30°	38056
35°	13679
40°	3435
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 0 cd/sqm

TEST NUMBER: P1303747

CATALOG NUMBER: P3DUS17R409040DE010 E3CBUS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	525.3	25.8
10°-20°	1107.1	54.4
20°-30°	364.3	17.9
30°-40°	36.7	1.8
40°-50°	1.6	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1996.7	98.1
0°-40°	2033.4	99.9
0°-60°	2035.0	100.0
0°-90°	2035.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2035.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5706	
5°	5631	525
15°	4230	1107
25°	637	364
35°	51	37
45°	0	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1303747

CATALOG NUMBER: P3DUS17R409040DE010 E3CBUS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	5705.8
2.5°	5696.8
5°	5630.7
7.5°	5492.4
10°	5233.9
12.5°	4834.0
15°	4229.8
17.5°	3397.0
20°	2278.7
22.5°	1229.6
25°	637.3
27.5°	303.6
30°	150.3
32.5°	84.2
35°	51.1
37.5°	27.1
40°	12.0
42.5°	3.0
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)