

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1304018

Luminaire Tested: P3DUS10R129727DE010 E3CBUS1MB

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1304018  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-24)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3DUS10R129727DE010 E3CBUS1MB  
Description: 3in Adjustable LED luminaire with, R12 optic, 2700K CCT AND, 97CRI , E3CBUS1MB TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 751.0 lumens  
Efficiency: N/A  
Efficacy: 64.2 lumens/watt  
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.22  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 11.7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1304018

CATALOG NUMBER: P3DUS10R129727DE010 E3CBUS1MB

### Luminous Intensity Polar Plot



TEST NUMBER: P1304018

CATALOG NUMBER: P3DUS10R129727DE010 E3CBUS1MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |    | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |    | 10 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 98 | 97 |
| 1   | 116 | 114 | 113 | 111 | 114 | 112 | 111 | 109 | 108 | 107 | 106 | 104 | 104 | 103 | 101 | 101 | 100 | 98  | 95 | 94 |
| 2   | 113 | 110 | 108 | 106 | 111 | 108 | 106 | 104 | 105 | 104 | 102 | 103 | 101 | 100 | 100 | 99  | 98  | 95  | 92 | 91 |
| 3   | 110 | 107 | 104 | 102 | 109 | 105 | 103 | 101 | 103 | 101 | 99  | 101 | 99  | 98  | 99  | 98  | 96  | 95  | 92 | 91 |
| 4   | 108 | 104 | 101 | 98  | 107 | 103 | 100 | 98  | 101 | 99  | 97  | 99  | 97  | 96  | 98  | 96  | 95  | 94  | 92 | 91 |
| 5   | 106 | 102 | 98  | 96  | 105 | 101 | 98  | 96  | 99  | 97  | 95  | 98  | 96  | 94  | 97  | 95  | 93  | 92  | 91 | 90 |
| 6   | 104 | 99  | 96  | 94  | 103 | 99  | 96  | 94  | 98  | 95  | 93  | 96  | 94  | 93  | 95  | 93  | 92  | 91  | 90 | 89 |
| 7   | 102 | 98  | 94  | 92  | 101 | 97  | 94  | 92  | 96  | 93  | 92  | 95  | 93  | 91  | 94  | 92  | 91  | 90  | 89 | 88 |
| 8   | 101 | 96  | 93  | 91  | 100 | 95  | 93  | 90  | 95  | 92  | 90  | 94  | 92  | 90  | 93  | 91  | 90  | 89  | 88 | 87 |
| 9   | 99  | 94  | 91  | 89  | 98  | 94  | 91  | 89  | 93  | 91  | 89  | 93  | 90  | 89  | 92  | 90  | 88  | 87  | 86 | 85 |
| 10  | 98  | 93  | 90  | 88  | 97  | 93  | 90  | 88  | 92  | 90  | 88  | 91  | 89  | 88  | 91  | 89  | 87  | 86  | 85 | 84 |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 2426121 |
| 5°  | 1567594 |
| 10° | 442299  |
| 15° | 125063  |
| 20° | 52295   |
| 25° | 23155   |
| 30° | 11825   |
| 35° | 6237    |
| 40° | 2662    |
| 45° | 713     |
| 50° | 785     |
| 55° | 0       |
| 60° | 0       |
| 65° | 0       |
| 70° | 0       |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 50°

Luminance: 785 cd/sqm

TEST NUMBER: P1304018

CATALOG NUMBER: P3DUS10R129727DE010 E3CBUS1MB

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 501.8  | 66.8      |
| 10°-20°   | 182.0  | 24.2      |
| 20°-30°   | 48.7   | 6.5       |
| 30°-40°   | 15.3   | 2.0       |
| 40°-50°   | 2.9    | 0.4       |
| 50°-60°   | 0.2    | 0.0       |
| 60°-70°   | 0.0    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 732.6  | 97.5      |
| 0°-40°    | 747.9  | 99.6      |
| 0°-60°    | 751.0  | 100.0     |
| 0°-90°    | 751.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 751.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°    | Flux |
|-----|-------|------|
| 0°  | 11064 |      |
| 5°  | 7122  | 502  |
| 15° | 551   | 182  |
| 25° | 96    | 49   |
| 35° | 23    | 15   |
| 45° | 2     | 3    |
| 55° | 0     | 0    |
| 65° | 0     | 0    |
| 75° | 0     | 0    |
| 85° | 0     | 0    |
| 90° | 0     |      |

TEST NUMBER: P1304018

CATALOG NUMBER: P3DUS10R129727DE010 E3CBUS1MB

**CANDELA DISTRIBUTION (FULL):**

| 0°    |         |
|-------|---------|
| 0°    | 11064.0 |
| 1°    | 10877.3 |
| 2°    | 10352.1 |
| 3°    | 9453.4  |
| 4°    | 8337.7  |
| 5°    | 7121.6  |
| 6°    | 5854.1  |
| 7°    | 4719.7  |
| 8°    | 3632.0  |
| 9°    | 2703.0  |
| 10°   | 1986.4  |
| 11°   | 1463.5  |
| 12°   | 1101.7  |
| 13°   | 854.3   |
| 14°   | 676.9   |
| 15°   | 550.9   |
| 17.5° | 350.1   |
| 20°   | 224.1   |
| 22.5° | 144.7   |
| 25°   | 95.7    |
| 27.5° | 65.4    |
| 30°   | 46.7    |
| 32.5° | 32.7    |
| 35°   | 23.3    |
| 37.5° | 16.3    |
| 40°   | 9.3     |
| 42.5° | 4.7     |
| 45°   | 2.3     |
| 47.5° | 2.3     |
| 50°   | 2.3     |
| 52.5° | 0.0     |
| 55°   | 0.0     |
| 57.5° | 0.0     |
| 60°   | 0.0     |
| 62.5° | 0.0     |
| 65°   | 0.0     |
| 67.5° | 0.0     |
| 70°   | 0.0     |
| 72.5° | 0.0     |
| 75°   | 0.0     |
| 77.5° | 0.0     |
| 80°   | 0.0     |
| 82.5° | 0.0     |
| 85°   | 0.0     |
| 87.5° | 0.0     |



TEST NUMBER: P1304018

CATALOG NUMBER: P3DUS10R129727DE010 E3CBUS1MB

CANDELA DISTRIBUTION (continued):



(END OF REPORT)