

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1304057

Luminaire Tested: P3DUS17R709727DE010 E3CBUS1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1304057
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-95)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3DUS17R709727DE010 E3CBUS1MW
Description: 3in Adjustable LED luminaire with, R70 optic, 2700K CCT AND, 97CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1353.0 lumens
Efficiency: N/A
Efficacy: 63.8 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.99
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1304057
CATALOG NUMBER: P3DUS17R709727DE010 E3CBUS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1304057
 CATALOG NUMBER: P3DUS17R709727DE010 E3CBUS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	107	105	105	103	101	101	100	98	98	96	95	94			
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87			
3	103	96	91	88	101	95	90	87	92	89	85	90	87	84	88	85	83	81			
4	98	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71			
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66			
7	83	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	62	59	66	62	59	57			
9	75	66	60	56	74	65	60	56	64	59	56	63	59	55	63	58	55	54			
10	72	62	56	52	71	62	56	52	61	56	52	60	55	52	59	55	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	329053
5°	313294
10°	299727
15°	285927
20°	264390
25°	239578
30°	206867
35°	186126
40°	72364
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 0 cd/sqm



TEST NUMBER: P1304057

CATALOG NUMBER: P3DUS17R709727DE010 E3CBUS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.5	9.9
10°-20°	351.9	26.0
20°-30°	450.2	33.3
30°-40°	388.6	28.7
40°-50°	28.9	2.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	935.5	69.1
0°-40°	1324.1	97.9
0°-60°	1353.0	100.0
0°-90°	1353.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1353.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1501	
5°	1423	133
15°	1260	352
25°	990	450
35°	695	389
45°	0	29
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1304057
CATALOG NUMBER: P3DUS17R709727DE010 E3CBUS1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1500.6
2.5°	1477.2
5°	1423.3
7.5°	1376.5
10°	1346.1
12.5°	1308.6
15°	1259.5
17.5°	1200.9
20°	1133.0
22.5°	1058.1
25°	990.2
27.5°	903.6
30°	817.0
32.5°	781.9
35°	695.3
37.5°	505.7
40°	252.8
42.5°	32.8
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)