

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1304088

Luminaire Tested: P3DUS02R089730DE010 E3CBUS1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1304088
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2408-211-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3DUS02R089730DE010 E3CBUS1MMS
Description: 3in Adjustable LED luminaire with, R08 optic, 3000K CCT AND, 97CRI , E3CBUS1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 221.0 lumens
Efficiency: N/A
Efficacy: 45.1 lumens/watt
Spacing Criteria (0/90/45): 0.16 / 0.16 / 0.16
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 4.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1304088

CATALOG NUMBER: P3DUS02R089730DE010 E3CBUS1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1304088

CATALOG NUMBER: P3DUS02R089730DE010 E3CBUS1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100
1	116	114	113	111	114	112	111	110	108	107	106	105	104	103	101	101	100	99	99	99
2	113	111	108	106	111	109	107	105	106	104	103	103	102	101	101	100	99	97	97	97
3	111	107	105	103	109	106	104	102	104	102	100	102	100	99	100	98	97	96	96	96
4	109	105	102	100	108	104	101	99	102	100	98	100	99	97	99	97	96	95	95	95
5	107	103	100	98	106	102	99	97	101	98	97	99	97	96	98	96	95	94	94	94
6	105	101	98	96	104	100	98	96	99	97	95	98	96	95	97	95	94	93	93	93
7	104	99	97	95	103	99	96	94	98	96	94	97	95	94	96	94	93	92	92	92
8	103	98	95	93	102	98	95	93	97	95	93	96	94	93	95	94	92	91	91	91
9	101	97	94	92	101	97	94	92	96	94	92	95	93	92	95	93	92	91	91	91
10	100	96	93	91	100	96	93	91	95	93	91	94	92	91	94	92	91	90	90	90

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1253430
5°	522671
10°	84122
15°	24109
20°	8121
25°	3581
30°	1975
35°	1392
40°	1260
45°	806
50°	580
55°	344
60°	395
65°	467
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 806 cd/sqm

TEST NUMBER: P1304088

CATALOG NUMBER: P3DUS02R089730DE010 E3CBUS1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	170.5	77.1
10°-20°	35.7	16.1
20°-30°	7.8	3.5
30°-40°	3.4	1.5
40°-50°	2.1	0.9
50°-60°	0.9	0.4
60°-70°	0.8	0.4
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	213.9	96.8
0°-40°	217.3	98.3
0°-60°	220.3	99.6
0°-90°	221.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	221.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5716	
5°	2374	170
15°	106	36
25°	15	8
35°	5	3
45°	3	2
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1304088

CATALOG NUMBER: P3DUS02R089730DE010 E3CBUS1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	5716.1
2.5°	4777.8
5°	2374.5
7.5°	885.2
10°	377.8
12.5°	195.0
15°	106.2
17.5°	60.1
20°	34.8
22.5°	22.6
25°	14.8
27.5°	11.3
30°	7.8
32.5°	6.1
35°	5.2
37.5°	4.4
40°	4.4
42.5°	3.5
45°	2.6
47.5°	1.7
50°	1.7
52.5°	0.9
55°	0.9
57.5°	0.9
60°	0.9
62.5°	0.9
65°	0.9
67.5°	0.9
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)