

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1305833

Luminaire Tested: P3SQASS09R709024DE010 E3SQCD1MB

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1305833
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3SQASS09R709024DE010 E3SQCD1MB
Description: 3in Adjustable LED luminaire with, R70 optic, 2400K CCT AND, 90CRI , E3SQCD1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 764.0 lumens
Efficiency: N/A
Efficacy: 68.8 lumens/watt
Spacing Criteria (0/90/45): 1 / 0.99 / 1.03
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1305833

CATALOG NUMBER: P3SQASS09R709024DE010 E3SQCD1MB

Luminous Intensity Polar Plot



TEST NUMBER: P1305833

CATALOG NUMBER: P3SQASS09R709024DE010 E3SQCD1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	98	95	105	101	97	94	98	95	92		95	92	90		92
3	102	95	90	86	100	94	89	85	91	87	84		89	86	83		87
4	96	89	83	79	95	88	82	78	85	81	77		83	79	76		81
5	91	83	77	72	90	82	76	72	80	75	71		78	74	71		77
6	86	77	71	67	85	76	71	66	75	70	66		73	69	65		72
7	82	72	66	62	80	71	66	61	70	65	61		69	64	61		68
8	78	68	61	57	76	67	61	57	66	61	57		65	60	57		64
9	74	63	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	59	53	50	58	53	49		58	53	49		57

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	127186	127186	127186
5°	122088	121414	121086
10°	117274	116260	116033
15°	114503	112898	113130
20°	109654	108591	108352
25°	101778	102025	100429
30°	93149	94441	90842
35°	76214	79872	73207
40°	43863	51124	45032
45°	633	21238	2192
50°	0	2251	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 21238 cd/sqm

TEST NUMBER: P1305833

CATALOG NUMBER: P3SQASS09R709024DE010 E3SQCD1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.9	8.6
10°-20°	178.5	23.4
20°-30°	245.3	32.1
30°-40°	222.4	29.1
40°-50°	51.7	6.8
50°-60°	0.3	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	489.7	64.1
0°-40°	712.1	93.2
0°-60°	764.0	100.0
0°-90°	764.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	764.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	738	738	738	738	738	
5°	706	704	702	701	700	66
15°	642	638	633	633	634	180
25°	536	538	537	532	528	246
35°	362	368	380	364	348	218
45°	3	29	87	38	9	31
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	

TEST NUMBER: P1305833

CATALOG NUMBER: P3SQASS09R709024DE010 E3SQCD1MB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	738.5	738.5	738.5	738.5	738.5
1°	737.8	736.5	737.2	737.8	738.5
2°	732.0	730.7	730.7	731.4	731.4
3°	724.9	722.3	722.3	721.7	721.7
4°	715.2	713.3	712.0	711.3	711.3
5°	706.2	704.2	702.3	701.0	700.4
6°	698.4	695.2	692.6	692.0	692.6
7°	689.4	687.4	684.8	682.9	683.6
8°	682.9	680.3	677.1	675.8	675.8
9°	677.1	674.5	671.3	668.7	670.0
10°	670.6	668.0	664.8	662.9	663.5
11°	666.1	662.9	659.0	657.7	658.4
12°	660.9	657.1	653.2	652.5	653.8
13°	654.5	650.6	646.7	646.7	648.0
14°	648.7	644.1	640.3	640.3	642.2
15°	642.2	637.7	633.2	633.2	634.5
17.5°	622.8	618.9	614.4	614.4	615.1
20°	598.3	596.3	592.5	590.5	591.2
22.5°	567.3	567.3	565.3	562.1	560.8
25°	535.6	538.2	536.9	531.7	528.5
27.5°	502.7	507.2	507.8	500.1	494.3
30°	468.4	472.3	474.9	465.8	456.8
32.5°	418.0	429.6	436.1	423.8	405.1
35°	362.5	367.6	379.9	363.7	348.2
37.5°	294.6	301.1	311.4	298.5	289.4
40°	195.1	221.0	227.4	221.0	200.3
42.5°	70.4	124.0	149.2	126.6	82.7
45°	2.6	29.1	87.2	37.5	9.0
47.5°	0.0	0.6	39.4	1.3	0.0
50°	0.0	0.0	8.4	0.0	0.0
52.5°	0.0	0.0	0.6	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1305833
CATALOG NUMBER: P3SQASS09R709024DE010 E3SQCD1MB

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)