

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1304508

Luminaire Tested: P3DUS05R609740DE010 E3CBUS1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1304508
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-93)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3DUS05R609740DE010 E3CBUS1MW
Description: 3in Adjustable LED luminaire with, R60 optic, 4000K CCT AND, 97CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 664.0 lumens
Efficiency: N/A
Efficacy: 92.2 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.84
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1304508

CATALOG NUMBER: P3DUS05R609740DE010 E3CBUS1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1304508

CATALOG NUMBER: P3DUS05R609740DE010 E3CBUS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94	92	90	89
3	104	98	93	89	102	96	92	89	94	90	87		91	88	86		89	87	85	83
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85	82	79	78
5	94	86	81	77	93	86	80	77	84	79	76		82	78	75		81	77	75	73
6	90	82	76	72	89	81	76	72	79	75	71		78	74	71		77	73	70	69
7	86	77	71	68	85	76	71	67	75	70	67		74	70	67		73	69	66	65
8	82	73	67	63	81	72	67	63	71	67	63		70	66	63		69	66	63	61
9	78	69	64	60	77	69	63	60	68	63	60		67	63	59		66	62	59	58
10	75	66	60	57	74	65	60	56	64	60	56		64	59	56		63	59	56	55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	187024
5°	181488
10°	183118
15°	176664
20°	149440
25°	121362
30°	89735
35°	62212
40°	22270
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 0 cd/sqm

TEST NUMBER: P1304508

CATALOG NUMBER: P3DUS05R609740DE010 E3CBUS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.8	11.9
10°-20°	212.7	32.0
20°-30°	226.6	34.1
30°-40°	137.7	20.7
40°-50°	8.2	1.2
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	518.1	78.0
0°-40°	655.8	98.8
0°-60°	664.0	100.0
0°-90°	664.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	664.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	853	
5°	824	79
15°	778	213
25°	502	227
35°	232	138
45°	0	8
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1304508

CATALOG NUMBER: P3DUS05R609740DE010 E3CBUS1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	852.9
2.5°	840.2
5°	824.5
7.5°	820.3
10°	822.4
12.5°	812.9
15°	778.2
17.5°	717.2
20°	640.4
22.5°	566.8
25°	501.6
27.5°	425.9
30°	354.4
32.5°	298.7
35°	232.4
37.5°	151.4
40°	77.8
42.5°	6.3
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)