

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1304857

Luminaire Tested: P3DUS02R25B2750DE010 E3CBUS1MW\_5000K

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1304857  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-87)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3DUS02R25B2750DE010 E3CBUS1MW\_5000K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R25 optic, 5000K CCT AND, 80CRI , E3CBUS1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 297.0 lumens  
Efficiency: N/A  
Efficacy: 102.4 lumens/watt  
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.39  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 2.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1304857  
CATALOG NUMBER: P3DUS02R25B2750DE010 E3CBUS1MW\_5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1304857  
 CATALOG NUMBER: P3DUS02R25B2750DE010 E3CBUS1MW\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102		100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99		97
2	112	109	106	104	110	107	105	103	104	102	100	101	100	98	99	97	96		95
3	109	105	101	99	107	103	100	98	101	99	97	99	97	95	97	95	94		92
4	106	101	98	95	105	100	97	94	98	95	93	96	94	92	95	93	91		90
5	103	98	94	92	102	97	94	91	96	93	90	94	92	90	93	91	89		88
6	101	95	91	89	100	95	91	88	93	90	88	92	89	87	91	89	87		86
7	98	93	89	86	97	92	89	86	91	88	86	90	87	85	89	87	85		84
8	96	90	87	84	95	90	86	84	89	86	84	88	85	83	87	85	83		82
9	94	88	84	82	93	88	84	82	87	84	82	86	83	81	86	83	81		80
10	92	86	83	80	91	86	82	80	85	82	80	84	82	80	84	81	80		79

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	342626
5°	317367
10°	238985
15°	111056
20°	34956
25°	13525
30°	3925
35°	1258
40°	401
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 0 cd/sqm



TEST NUMBER: P1304857

CATALOG NUMBER: P3DUS02R25B2750DE010 E3CBUS1MW\_5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	126.0	42.4
10°-20°	138.8	46.7
20°-30°	28.5	9.6
30°-40°	3.5	1.2
40°-50°	0.2	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	293.3	98.8
0°-40°	296.8	99.9
0°-60°	297.0	100.0
0°-90°	297.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	297.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1562	
5°	1442	126
15°	489	139
25°	56	29
35°	5	3
45°	0	0
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1304857  
CATALOG NUMBER: P3DUS02R25B2750DE010 E3CBUS1MW\_5000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1562.5
2.5°	1532.4
5°	1441.8
7.5°	1290.2
10°	1073.3
12.5°	790.6
15°	489.2
17.5°	266.2
20°	149.8
22.5°	91.6
25°	55.9
27.5°	31.5
30°	15.5
32.5°	7.0
35°	4.7
37.5°	2.8
40°	1.4
42.5°	0.5
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)