

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1304871

Luminaire Tested: P3DUS02R40B2750DE010 E3CBUS1MW_4000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1304871
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-90)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3DUS02R40B2750DE010 E3CBUS1MW_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R40 optic, 4000K CCT AND, 80CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 297.0 lumens
Efficiency: N/A
Efficacy: 102.4 lumens/watt
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.55
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 2.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1304871

CATALOG NUMBER: P3DUS02R40B2750DE010 E3CBUS1MW_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1304871

CATALOG NUMBER: P3DUS02R40B2750DE010 E3CBUS1MW_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	113	111	109	107	107	105	104		103	102	101		100
2	111	107	104	102	109	106	103	101	103	100	98		100	98	96		97
3	107	103	99	96	106	101	98	95	99	96	94		97	94	92		94
4	104	98	94	91	102	97	94	91	95	92	90		94	91	89		92
5	101	95	90	87	99	94	90	87	92	89	86		91	88	86		89
6	98	91	87	84	96	90	86	84	89	86	83		88	85	83		87
7	95	88	84	81	94	87	83	80	86	83	80		85	82	80		84
8	92	85	81	78	91	85	80	78	84	80	77		83	79	77		82
9	89	82	78	75	88	82	78	75	81	77	75		80	77	75		80
10	87	80	76	73	86	79	75	73	79	75	73		78	75	72		77

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	182595
5°	180893
10°	170093
15°	140137
20°	77613
25°	22501
30°	5545
35°	2008
40°	515
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 0 cd/sqm

TEST NUMBER: P1304871

CATALOG NUMBER: P3DUS02R40B2750DE010 E3CBUS1MW_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.7	25.8
10°-20°	161.6	54.4
20°-30°	53.2	17.9
30°-40°	5.4	1.8
40°-50°	0.2	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	291.4	98.1
0°-40°	296.8	99.9
0°-60°	297.0	100.0
0°-90°	297.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	297.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	833	
5°	822	77
15°	617	162
25°	93	53
35°	8	5
45°	0	0
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1304871

CATALOG NUMBER: P3DUS02R40B2750DE010 E3CBUS1MW_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	832.7
2.5°	831.4
5°	821.8
7.5°	801.6
10°	763.9
12.5°	705.5
15°	617.3
17.5°	495.8
20°	332.6
22.5°	179.4
25°	93.0
27.5°	44.3
30°	21.9
32.5°	12.3
35°	7.5
37.5°	3.9
40°	1.8
42.5°	0.4
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)