

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1304876

Luminaire Tested: P3DUS02R45B2750DE010 E3CBUS1MW_4000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1304876
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-96)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3DUS02R45B2750DE010 E3CBUS1MW_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R45 optic, 4000K CCT AND, 80CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 299.0 lumens
Efficiency: N/A
Efficacy: 103.1 lumens/watt
Spacing Criteria (0/90/45): 0.67 / 0.67 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 2.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1304876

CATALOG NUMBER: P3DUS02R45B2750DE010 E3CBUS1MW_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1304876

CATALOG NUMBER: P3DUS02R45B2750DE010 E3CBUS1MW_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20				20				20
RC	80				70				50				30				10				0				0				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100											
1	115	112	110	108	112	110	108	107	106	105	103	102	101	100	99	98	97	96											
2	110	106	103	100	108	105	102	99	101	99	97	99	97	95	96	94	93	91											
3	106	101	97	94	104	100	96	93	97	94	92	95	92	90	93	91	89	87											
4	102	96	92	88	101	95	91	88	93	90	87	91	88	86	89	87	85	84											
5	98	92	87	84	97	91	87	83	89	86	83	88	85	82	86	84	81	80											
6	95	88	83	80	94	87	83	79	86	82	79	84	81	78	83	80	78	77											
7	92	84	79	76	90	84	79	76	82	78	76	81	78	75	80	77	75	74											
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	78	74	72	71											
9	85	78	73	70	84	77	73	70	76	72	70	76	72	69	75	72	69	68											
10	82	75	70	67	82	74	70	67	74	70	67	73	69	67	72	69	66	65											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	145032
5°	144244
10°	135624
15°	110875
20°	81277
25°	45051
30°	18003
35°	5889
40°	1374
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 0 cd/sqm

TEST NUMBER: P1304876

CATALOG NUMBER: P3DUS02R45B2750DE010 E3CBUS1MW_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.2	20.5
10°-20°	133.8	44.7
20°-30°	86.7	29.0
30°-40°	16.8	5.6
40°-50°	0.6	0.2
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	281.6	94.2
0°-40°	298.4	99.8
0°-60°	299.0	100.0
0°-90°	299.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	299.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	661	
5°	655	61
15°	488	134
25°	186	87
35°	22	17
45°	0	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1304876

CATALOG NUMBER: P3DUS02R45B2750DE010 E3CBUS1MW_4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	661.4
2.5°	661.0
5°	655.3
7.5°	641.2
10°	609.1
12.5°	554.7
15°	488.4
17.5°	419.9
20°	348.3
22.5°	265.3
25°	186.2
27.5°	120.8
30°	71.1
32.5°	40.4
35°	22.0
37.5°	11.4
40°	4.8
42.5°	0.9
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)